

LogiLink®



Industrial Gigabit Ethernet Switch, 4-Port 1000 Mbps + 1-Port SFP

Art. No.: NS204

Compact size 5-Port 10/100/1000 Base-TX Ethernet Switch, suitable for industrial application. Featuring four 10/100/1000Base-TX RJ45 and one SFP ports, IP40-rated rugged aluminum case and a wide-ranging redundant power system (12–52 V DC). It is able to operate in any harsh environment with operating temperature ranging from -40 to 80°C.

Features:

- » Industrial switch, 4x 10/100/1000Base-TX RJ45 and 1x SFP ports
- » Unmanaged, easy installation, plug-and-play
- » Compact and rugged metal housing, IP40
- » Free fall, shock and vibration stability
- » Power input: 12 to 52 V DC redundant power
- » Extended operation temperature: -40–80°C
- » Suitable for DIN-rail mounting



Specification:

Protocols/Standards	IEEE 802.3, IEEE 802.3i, IEEE 802.3u, IEEE 802.3x, IEEE 802.3ab, IEEE 802.3z
Interface	4x 10/100/1000 Mbps RJ45 ports + 1x SFP slot
Bandwidth	14 Gbps
Packet Buffer Memory	1.2 Mbit
Packet Forwarding Rate	10.5 Mpps
MAC Address Table	2K
Flow Control	Back pressure for half duplex, IEEE 802.3x pause frame for full duplex
LED Indicator	Power: Red; Ethernet: Yellow; SPF: Green
Network Cables	10Base-T: Cat.3/4/5 UTP (≤100 m); 100Base-Tx: Cat.5 or later UTP (≤100 m) 1000BASE-TX: Cat.6 or later UTP (≤100 m)
Power Input	12–52 V DC redundant power
Power Consumption	Max. 3 W



NS204



Made in China



*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.

Installation	DIN rail
Enclosure	IP40 aluminum housing
MTBF	>300,000 hours
Operating Temperature	-40~80°C
Storage Temperature	-40~80°C
Storage Humidity	5~95% RH non-condensing
Dimension	11.8 x 8.6 x 3.35 cm
Weight	0.36 kg



Package Contents:

- » 1 x Gigabit Ethernet Switch
- » 1 x User Manual

Package Information:

- » Packing Dimension: 165 x 135 x 54 mm
- » Packing Weight: 0.46 kg
- » Carton Dimension: 445 x 350 x 343 mm
- » Carton Q'ty: 36 pcs
- » Carton Weight: 16.6 kg



*The specifications and pictures are subject to change without prior notice.
 *All trade names referenced are the registered trademarks of their respective owners.



NS204



4 052792 070460

Made in China