



EHI C€ KK

Features

- SMD package with industry standard pinout
- Operating temperature range -40 ~ +100°C
- · High efficiency up to 83%
- 2KVDC I/O isolation
- · Low cost
- 3 years warranty











Applications

- Telecom/datacom system
- · Wireless network
- Industrial control facility
- Instrument
- Analyzer
- Detector
- · Data switch


■ GTIN CODE

MW Search: https://www.meanwell.com/serviceGTIN.aspx

■ Description

SBTN01-N series is 1W isolated and unregulated module type DC-DC converter with SMD package. It features international standard pins, a high efficiency up to 83%, wide working temperature range -40~+100 $^{\circ}$ C, 2KVDC I/P-O/P isolation voltage, compliance to BS EN/EN55032. The models account for different input voltage 5V/12V/24V±10%, and various output voltage, 5V/12V/15V for single output which are suitable for all kinds of systems, Such as industrial control, telecommunication field, distributed power architecture, and so on.

■ Model Encoding





MODEL SELECTION TABLE							
ORDER NO.	INPUT			OUTPUT			
	INPUT VOLTAGE	INPUT CURRENT		OUTPUT	OUTPUT	EFFICIENCY (TYP.)	CAPACITOR LOAD (MAX.)
	(RANGE)	NO LOAD	FULL LOAD	VOLTAGE	CURRENT	, ,	(2)
SBTN01L-05N		30mA	270mA	5V	20 ~ 200mA	77%	1000μF
SBTN01L-12N	5V (4.5 ~ 5.5V)	30mA	257mA	12V	8.4 ~ 84mA	78%	330µF
SBTN01L-15N		30mA	253mA	15V	6.7 ~ 67mA	79%	220μF
SBTN01M-05N		12mA	112mA	5V	20 ~ 200mA	73%	1000µF
SBTN01M-12N	12V (10.8 ~ 13.2V)	12mA	102mA	12V	8.4 ~ 84mA	80%	330µF
SBTN01M-15N		12mA	102mA	15V	6.7 ~ 67mA	83%	220μF
SBTN01N-05N		11mA	54mA	5V	20 ~ 200mA	73%	1000μF
SBTN01N-12N	24V (21.6 ~ 26.4V)	11mA	54mA	12V	8.4 ~ 84mA	80%	330µF
SBTN01N-15N		11mA	54mA	15V	6.7 ~ 67mA	81%	220μF





SPECIFICA	TION						
	VOLTAGE RANGE	L: 4.5 ~ 5.5Vdc , M: 10.8 ~ 13.2Vdc , N: 21.6 ~ 26.4Vdc					
INPUT	FILTER	Internal capacitor					
	PROTECTION	Fuse recommended. 5Vin models: 750mA Slow-Blow Type, 12Vin models: 300mA Slow-Blow Type, 24Vin models: 150mA Slow-Blow Type					
	INTERNAL POWER DISSIPATION						
	VOLTAGE ACCURACY	±5.0%					
	RATED POWER	1W					
	RIPPLE & NOISE Note.2	100mVp-p					
	LINE REGULATION Note.3	1.2% for 1% input variation					
	LOAD REGULATION Note.4	5Vo: ±15%, 12/15Vo: ±10%					
	SWITCHING FREQUENCY (Typ.)						
PROTECTION	SHORT CIRCUIT	0.5 second max.					
	COOLING	Free-air convection					
	WORKING TEMP.	-40 ~ +100°C (Refer to "Derating Curve")					
	CASE TEMPERATURE	+100°C max.					
	WORKING HUMIDITY	20% ~ 90% RH non-condensing					
ENVIRONMENT	STORAGE TEMP., HUMIDITY	-55 ~ +125°C, 10 ~ 95% RH non-condensing					
	TEMP. COEFFICIENT	0.03% / °C (0 ~ 85°C)					
	SOLDERING TEMPERATURE	1.5mm from case of 1 \sim 10sec./240 $^{\circ}$ C max.					
	VIBRATION	10 ~ 500Hz, 2G 10min./1cycle, period for 60min. each along X, Y, Z axes					
	SAFETY STANDARDS	EAC TP TC 020/2011 approved					
	WITHSTAND VOLTAGE	I/P-O/P:2KVDC					
	ISOLATION RESISTANCE	I/P-O/P:10G Ohms / 500VDC / 25°C / 70% RH					
	ISOLATION CAPACITANCE (Typ.)	75pF					
SAFETY &	EMC EMISSION	Parameter	Standard	Test Level / Note(Note.6)			
EMC		Conducted	BS EN/EN55032(CISPR32)	Class A/B with external components			
(Note.5)		Radiated	BS EN/EN55032(CISPR32)	(see page 5)			
	EMC IMMUNITY	Parameter	Standard	Test Level / Note			
		ESD	BS EN/EN61000-4-2	\pm 8KV air ; \pm 6KV contact, Criterion B			
		Radiated Susceptibility	BS EN/EN61000-4-3	3V/m, Criterion A			
		EFT/Burest	BS EN/EN61000-4-4	1KV at power, Criterion B			
		Surge	BS EN/EN61000-4-5	0.5KV Line-Line, Criterion B			
		Conducted	BS EN/EN61000-4-6	3Vrms, Criterion A			
		Magnetic Field	BS EN/EN61000-4-8	1A/m, Criterion A			
	MTBF	955Khrs max. MIL-HDBK-217F(25°C)					
	DIMENSION (L*W*H)	12.9*10.9*7.1mm (0.50*0.43*0.28 inch)					
OTHERS	CASE MATERIAL	Non-Conductive black plastic (UL 94V-0 rated)					
	PACKING	1.0g					
NOTE	2.Ripple & noise are mea 3.Line regulation is meas 4.Load regulation is meas 5.The final equipment murefer to "EMI testing of 6.An external input filter control The filter capacitor Pow	rameters are specified at normal input(L:5Vdc, M:12Vdc, N:24Vdc), rated load, 25°C 70% RH ambient. & noise are measured at 20MHz by using a 12" twisted pair terminated with a 0.1µf & 47µf capacitor. egulation is measured from low line to high line at rated load. regulation is measured from 10% to 100% rated load. regulation is measured from 10% to 100% rated load. real equipment must be re-confirm that it still meet EMC directives. For guidance on how to perform these EMC tests, please of "EMI testing of component power supplies." (as available on http://www.meanwell.com) remaining the respective of the module has to meet BS EN/EN61000-4-4, BS EN/EN61000-4-5. ter capacitor Power Mate suggest: 220uF/100V. ret Liability Disclaimer: For detailed information, please refer to https://www.meanwell.com/serviceDisclaimer.aspx					





■ Mechanical Specification


- All dimensions in mm(inch)
- Tolerance:x.x±0.5mm(x.xx±0.02") $x.xx\pm0.25mm(x.xxx\pm0.01")$
- Pin size is 0.50x0.30mm (0.02" x0.01")
 Pin is Tolerance:x.xx±0.07mm(x.xxx±0.03")













■ Plug Assignment

Pin No.	Pin-Out		
1	-Vin		
2	+Vin		
4	-Vout		
5	+Vout		
8	N.C.		

■ Derating Curve



■ Reflow Soldering Curve




Remark: The curve applies only to the hot air reflow soldering.



■ EMC Suggestion Circuit

*Required external componets to meet BS EN/EN55032 Class A/B are as below:



Model No.	Clas	ss A	Class B		
Widder No.	L1	C1	L1	C1	
SBTN01L-xxN	2.2µH	2.2µF	10µH	2.2µF	
SBTN01M-xxN	6.8µH	2.2µF	6.8µH	4.7µF	
SBTN01N-xxN	22µH	4.7µF	22µH	4.7µF	

■ Packing

Standard Tube Packing	MPQ Per Tube (PCS)	One Box G.W.	Max. Q'TY/ Carton(PCS)	One Carton G.W.
Unit: mm 0.55 ± 0.2 7.7 ± 0.3 13.5 ± 0.5 17.0 ± 0.	40	0.071Kg	1440	3Kg

■ Installation Manual

Please refer to: http://www.meanwell.com/manual.html