



Part Number : [1301460080](#)

Product Description : Watertite Extreme Plug with Locking Blade, 2 Pole/3 Wire, NEMA L7-15, 277V, Cord Grip Body Size F2, Black, Silicone Husk

Series Number : 130146

Status : Active

Product Category : Wiring Devices

Engineering Number : 24W34BLK



Documents & Resources

Drawings

[Drawing 1301460080_sd.pdf](#)

3D Models and Design Files

[3D Model 1301460080_stp.zip](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Wiring Devices
Series	130146
Description	Watertite Extreme Plug with Locking Blade, 2 Pole/3 Wire, NEMA L7-15, 277V, Cord Grip Body Size F2, Black, Silicone Husk
IP Rating	IP69K
NEMA Configuration	NEMA L7-15
Product Family	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite Extreme
Specialty	N/A
Type	Plug
UPC	78678871255

Agency

CSA	LR6837
UL	E10176

Electrical

Current - Maximum per Contact	15.0A
GFCI	No
Voltage - Maximum	277V

Physical

Cord Grip Body Size	F2 1/2"
Cord Type	N/A
Flange	No
Flip Lid	No
Gender	Male

Length	N/A
Lighted Connector	No
Locking Blade	Yes
Net Weight	126.098/g
Poles	2-pole/3-wire
Receptacle Type	N/A

This document was generated on Sep 26, 2023