




Part Number : [530481110](#)
Product Description : 1.25mm Pitch,
PicoBlade PCB Header, Single Row, Right-
Angle, Through Hole, Tin (Sn) Plating, Friction
Lock, 11 Circuits, Tray, 2.30mm PC Tail
Length
Series Number : 53048
Status : Active
Product Category : PCB Headers and
Receptacles



Documents & Resources

- Drawings**
[Drawing 530481110_sd.pdf](#)
- 3D Models and Design Files**
[2D Drawing DXF 530481110.dxf](#)
[2D Drawing DXF \(PDF\) 530481110.pdf](#)
[3D Model 530481110_stp.zip](#)

- Specifications**
[Application Specification 510210000-AS-000.pdf](#)
[Packaging Specification SPK-53048-001-001.pdf](#)
[Product Specification 510211010-PS-000.pdf](#)
[Product Specification 510211111-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)
- Eu RoHS

- REACH SVHC

- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D

- Molex Product Compliance Declaration

- IEC-62474

- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	53048
Description	1.25mm Pitch, PicoBlade PCB Header, Single Row, Right-Angle, Through Hole, Tin (Sn) Plating, Friction Lock, 11 Circuits, Tray, 2.30mm PC Tail Length
Application	Signal, Wire-to-Board
Component Type	PCB Header
Product Family	PicoBlade Connector System
Product Name	PicoBlade
UPC	800753750210

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	125V

Physical

Breakaway	No
Circuits (Loaded)	11
Circuits (maximum)	11

Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Mated Height	3.50mm
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	255.670/mg
Number of Rows	1
Orientation	Right Angle
Packaging Type	Tray
PC Tail Length	2.30mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	0.80mm
Pitch - Mating Interface	1.25mm
Polarized to PCB	No
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Through Hole

Mates With / Use With

Mates with Part(s)

Description	Part Number
PicoBlade Single Row Receptacle Housings	<u>51021</u>