




**Part Number :** [459712115](#)

**Product Description :** 1.27mm Pitch, SEARAY Receptacle, 200 Circuits, 5.00mm Unmated Height, 10 Rows, with Pegs, Solder Charge Lead-Free

**Series Number :** 45971

**Status :** Active

**Product Category :** Board-to-Board Connectors



---

## Documents & Resources

### Drawings

[Drawing 459712115\\_sd.pdf](#)

[Packaging Design Drawing PK-45971-002-001.pdf](#)

### 3D Models and Design Files

[3D Model 459712115\\_stp.zip](#)

[Electrical Model Document EE-46556-0085-001.pdf](#)

[Electrical Model Document EE-45970-010-010.pdf](#)

[S-Parameter Model SP-45970-010-010.zip](#)

[S-Parameter Model SP-46556-0085-001.zip](#)

[Symbol Footprint Data SYM-45971-2115-001.zip](#)

### Specifications

[Application Specification AS-45970-002-001.pdf](#)

[Application Specification AS-45970-990-001.pdf](#)

[Application Specification AS-45970-001-001.pdf](#)

[Product Specification TS-45970-001-001.pdf](#)

[Product Specification PS-45970-002-001.pdf](#)

[Product Specification PS-45970-001-001.pdf](#)

[Test Summary TS-45970-002-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21

REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Board-to-Board Connectors
Series	45971
Description	1.27mm Pitch, SEARAY Receptacle, 200 Circuits, 5.00mm Unmated Height, 10 Rows, with Pegs, Solder Charge Lead-Free
Application	Board-to-Board, Signal
Component Type	PCB Receptacle
Product Family	SEARAY and SEARAY Slim Mezzanine Family
Product Name	SEARAY
UPC	883906233235

### Agency

CSA	LR19980
UL	E29179

### Electrical

Current - Maximum per Contact	2.7A
-------------------------------	------

Grounding to PCB	No
Voltage - Maximum	240V AC

## Physical

Circuits (Loaded)	200
Circuits (maximum)	200
Color - Resin	Black
Durability (mating cycles max)	100
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	No
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	2.352/g
Number of Rows	10
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Robotic Placement	Pick and Place Cap
Stackable	No
Temperature Range - Operating	-55° to +125°C
Termination Interface Style	Surface Mount
Unmated Height	5.00mm

## Solder Process Data

Max-Duration	3
Lead-Free Process Capability	REFLOW
Max-Cycle	1
Max-Temp	260

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
1.27mm Pitch, SEARAY Plugs	<u>45970</u>

---

This document was generated on Sep 26, 2023