




Part Number : [26202061](#)
Product Description : KK 396 Wire-to-Board Header, Vertical Round Pin, 6 Circuits, Tin (Sn) Plating, with Mating Pin Length of 11.43mm (.450")
Series Number : 3192
Status : Active
Product Category : PCB Headers and Receptacles
Engineering Number : 319206A



Documents & Resources

Drawings
[Drawing 026202061_sd.pdf](#)
[Packaging Design Drawing PK-3192-001-001.pdf](#)

3D Models and Design Files
[3D Model 026202061_stp.zip](#)
[Symbol Footprint Data SYM-26-20-2061-001.zip](#)

Specifications
[Product Specification PS-99020-0087-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	3192
Description	KK 396 Wire-to-Board Header, Vertical Round Pin, 6 Circuits, Tin (Sn) Plating, with Mating Pin Length of 11.43mm (.450")
Application	Board-to-Board, Power, Wire-to-Board
Component Type	PCB Header
Product Family	KK Interconnect Systems
Product Name	KK 396
UPC	800753735248

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	7.0A
Voltage - Maximum	250V

Physical

Breakaway	No
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Natural
Durability (mating cycles max)	25

First Mate / Last Break	No
Flammability	94V-2
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1.462/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Bag
PC Tail Length	4.45mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	3.96mm
Pitch - Termination Interface	3.96mm
Plating min - Mating	5.080μm
Plating min - Termination	5.080μm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	No
Stackable	Yes
Temperature Range - Operating	See Product Specification
Termination Interface Style	Through Hole

Solder Process Data

Max-Duration	5
Lead-Free Process Capability	WAVE
Max-Cycle	1
Max-Temp	235

Mates With / Use With

Mates with Part(s)

Description	Part Number
KK 3.96mm Single Row Crimp Housings	<u>3069</u>

This document was generated on Sep 26, 2023
