



Part Number : [192110002](#)

Product Description : Krimptite Wire Pin Terminal for 12-10 AWG Wire, Mylar Tape Carrier

Series Number : 19211

Status : Active

Product Category : Crimp Terminals

Engineering Number : WP-1210T

Packaging Alternative : 0192110001 (Bag)



Documents & Resources

Drawings

[Drawing 192110002_sd.pdf](#)


Specifications

[Product Specification PS-19902-011-001.pdf](#)

[Product Specification PS-19902-015-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Terminals
Series	19211
Description	Krimptite Wire Pin Terminal for 12-10 AWG Wire, Mylar Tape Carrier
Application	Power, Wire-to-Component
Comments	Pin Length 11.43mm
Product Family	Wire Pins
Product Name	Wire Pin
UPC	800753053205

Agency

CSA	LR18689
UL	E32244

Physical

Gender	Male
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.465/g
Packaging Type	Adhesive Tape on Reel
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	3.45mm max.
Wire Size (AWG)	10, 12

Wire Size mm ²	N/A
---------------------------	-----

Application Tooling

Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<u>0190270088</u>
Mini-Mac Applicator	<u>0638851000</u>

This document was generated on Sep 26, 2023