



Part Number : [192030011](#)

Product Description : Krimptite Temp-Term Ring Tongue Terminal for 18 to 22 AWG Wire, Stud Size 6 (M3.5), Mylar Tape Carrier

Series Number : 19203

Status : Active

Product Category : Ring and Spade Terminals

Engineering Number : A-S-132-06T



Documents & Resources

Drawings

[Drawing 192030011_sd.pdf](#)

3D Models and Design Files

[3D Model 192030011_stp.zip](#)


Specifications

[Product Specification PS-19902-011-001.pdf](#)

[Product Specification PS-19902-015-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19203
Description	Krimptite Temp-Term Ring Tongue Terminal for 18 to 22 AWG Wire, Stud Size 6 (M3.5), Mylar Tape Carrier
Keyword	Ring Terminal, Ring Terminals
Product Family	High-Temperature Temp Terms Terminals and Splices
Product Name	Krimptite,Temp-Terms
Type	Ring
UPC	800753049406

Agency

UL	E32244
----	--------

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Nickel
Net Weight	0.508/g
Packaging Type	Adhesive Tape on Reel
Stud Size	6 (M3.5)
Wire Size (AWG)	18, 20, 22
Wire Size mm ²	0.25-1.50

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<u>0190270026</u>
Mini-Mac Applicator	<u>0638854500</u>

This document was generated on Sep 26, 2023