




Part Number : [334680003](#)

Product Description : 2.54mm Pitch MX64 Terminal, Tin (Sn) Plating, 18-20 AWG, Right Reel Payoff, Also used with MX123 Female Receptacle Housing

Series Number : 33468

Status : Active

Product Category : Crimp Terminals



Documents & Resources

Drawings

[Drawing 334680003_sd.pdf](#)

[Packaging Design Drawing PK-30907-759-001.pdf](#)

[Packaging Design Drawing PK-31302-480-001.pdf](#)

Specifications

[Application Specification AS-33468-001-001.pdf](#)

[Product Specification PS-33468-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33; 34
China RoHS	
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Terminals
Series	33468
Description	2.54mm Pitch MX64 Terminal, Tin (Sn) Plating, 18-20 AWG, Right Reel Payoff, Also used with MX123 Female Receptacle Housing
Application	Automotive, Power, Wire-to-Board, Wire-to-Wire
Comments	Right Reel Payoff; For automatic and semi-automatic crimping, use Left Reel Payoff terminals. See Sales Drawing for Left Reel Payoff Part Numbers.
Product Family	MX64 Sealed Connectors
Product Name	MX123,MX64
UPC	756054744505

Physical

Gender	Female
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.220/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	1.905µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.50-2.06mm
Wire Size (AWG)	18, 20
Wire Size mm ²	N/A

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Use with Part(s)

Description	Part Number
MX64 Sealed Single Row Receptacle Housings	<u>31403</u>
MX123 Receptacle Housings	<u>34566</u>
MX123 Female Receptacle Housings	<u>34576</u>

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for 2.54mm MX64 Terminals, 18-22 AWG	<u>0638114200</u>
Extraction Tool for SPOX, MX64, Ditto, MX150CE, Milli-Grid Terminals	<u>0638131400</u>
