




Part Number : [351510210](#)

Product Description : VersaBlade Hybrid Plug Housing, 2 Circuits, Positive Lock, Natural

Series Number : 35151

Status : Active

Product Category : Connector Housings



---

## Documents & Resources

### Drawings

[Drawing 351510210\\_sd.pdf](#)

### 3D Models and Design Files

[3D Model 351510210\\_stp.zip](#)

### Specifications

[Application Specification 351500000AS\\_ENG-000.pdf](#)

[Packaging Specification PK-35151-003-001.pdf](#)

[Product Specification PS-35150-003-001.pdf](#)

[Product Specification PS-35150-001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

### [Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

### [Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Connector Housings
Series	35151
Description	VersaBlade Hybrid Plug Housing, 2 Circuits, Positive Lock, Natural
Application	Power, Wire-to-Wire
Product Family	VersaBlade Wire-to-Wire Connector System
Product Name	VersaBlade
UPC	800754375566

### Agency

CSA	LR19980
UL	E29179

### Physical

Circuits (maximum)	2
Color - Resin	Natural
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	1.726/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No

Pitch - Mating Interface	6.20mm
Pitch - Termination Interface	6.20mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +120°C

## Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
VersaBlade Multi-Module 2-3-4 Hybrid Receptacle Housing, 9 Circuits, Full Flange Panel Mount, Natural, Glow-Wire Capable	<u><a href="#">2026500909</a></u>
VersaBlade Hybrid Receptacles Housings and TPAs	<u><a href="#">35150</a></u>
VersaBlade Multi-Module 2-3-4 Hybrid Receptacle Housings	<u><a href="#">35524</a></u>

### Use with Part(s)

Description	Part Number
VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Natural	<u><a href="/content/molex/molex-dot-com/us/en/products/product-page.html/351500290.html">/content/molex/molex-dot-com/us/en/products/product-page.html/351500290.html</a></u>
VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Red	<u><a href="/content/molex/molex-dot-com/us/en/products/product-page.html/351500292.html">/content/molex/molex-dot-com/us/en/products/product-page.html/351500292.html</a></u>
VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Yellow	<u><a href="/content/molex/molex-dot-com/us/en/products/product-page.html/351500293.html">/content/molex/molex-dot-com/us/en/products/product-page.html/351500293.html</a></u>
VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Blue	<u><a href="/content/molex/molex-dot-com/us/en/products/product-page.html/351500294.html">/content/molex/molex-dot-com/us/en/products/product-page.html/351500294.html</a></u>
VersaBlade Female Crimp Terminals	<u><a href="#">35746</a></u>