




Part Number : [513533200](#)
Product Description : 2.00mm Pitch
MicroClasp Wire-to-Board Receptacle
Housing, Positive Lock, Dual Row, 32 Circuits,
White
Series Number : 51353
Status : Active
Product Category : Connector Housings



Documents & Resources

Drawings

[Drawing 513533200_sd.pdf](#)

3D Models and Design Files

[3D Model 513533200_stp.zip](#)

Specifications

[Application Specification 561340000-AS-000.pdf](#)

[Packaging Specification SPK-51353-001-001.pdf](#)

[Product Specification PS-51353-003-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Housings
Series	51353
Description	2.00mm Pitch MicroClasp Wire-to-Board Receptacle Housing, Positive Lock, Dual Row, 32 Circuits, White
Application	Signal, Wire-to-Board
Product Family	MicroClasp Wire-to-Board System
Product Name	MicroClasp
UPC	756054235867

Agency

UL	E29179
----	--------

Physical

Circuits (maximum)	32
Color - Resin	White
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1414.000/mg
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Stackable	No

Temperature Range - Operating	-40° to +105°C
-------------------------------	----------------

Mates With / Use With

Mates with Part(s)

Description	Part Number
MicroClasp Vertical Dual Row Headers	<u>501844</u>
MicroClasp Vertical Dual Row Headers	<u>55917</u>
MicroClasp Right-Angle Dual Row Headers	<u>55959</u>

Use with Part(s)

Description	Part Number
Pre-Crimped Lead MicroClasp Female-to-MicroClasp Female, Tin (Sn) Plating, 150.00mm Length, 24 AWG, Black	/content/molex/molex-dot-com/us/en/products/product-page.html/797581001.html
Pre-Crimped Lead MicroClasp Female-to-MicroClasp Female, Tin (Sn) Plating, 300.00mm Length, 24 AWG, Black	/content/molex/molex-dot-com/us/en/products/product-page.html/797581002.html
MicroClasp Terminal Position Assurance (TPA) Retainers	<u>500638</u>
2.00mm Pitch Female Crimp Terminals	<u>56134</u>