



Part Number : [733300030](#)
Product Description : 75 Ohms, F Right-Angle Printed Circuit Board Jack Receptacle
Series Number : 73330
Status : Active
Product Category : RF / Coaxial Connectors



Documents & Resources

- Drawings
[Drawing 733300030_sd.pdf](#)
- 3D Models and Design Files
[3D Model 733300030_stp.zip](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73330
Description	75 Ohms, F Right-Angle Printed Circuit Board Jack Receptacle
Product Family	Type F RF Connectors
Product Name	F
Style	PCB
Type	Miniature
UPC	800754883481

Electrical

Frequency	2 GHz
Impedance	75 Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level

Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	None
Net Weight	9.720/g
Orientation	Right Angle
Packaging Type	Bag
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	Through Hole
PCB Thickness - Recommended	2.40mm
Wire/Cable Type	N/A

Solder Process Data

Max-Duration	10
--------------	----

Lead-Free Process Capability	WAVE
Max-Cycle	30
Max-Temp	150