




Part Number : [903257006](#)
Product Description : Picoflex PF-50 Header, Vertical, Low Profile, with PCB Pegs, 6 Circuits, Selective Gold (Au) Plating, Tube Packaging
Series Number : 90325
Status : Active
Product Category : PCB Headers and Receptacles



Documents & Resources

Drawings
[Drawing 903257006_sd.pdf](#)

3D Models and Design Files
[3D Model 903257006_stp.zip](#)

Specifications
[Application Specification 908140000-AS-000.pdf](#)
[Packaging Specification PK-90325-001-001.pdf](#)
[Product Specification PS-99020-0011-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)
- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	90325
Description	Picoflex PF-50 Header, Vertical, Low Profile, with PCB Pegs, 6 Circuits, Selective Gold (Au) Plating, Tube Packaging
Application	Signal, Wire-to-Board
Comments	Low Profile
Component Type	PCB Header
Product Family	Picoflex Ribbon-Cable Connectors
Product Name	Picoflex
UPC	822350245661

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	1.2A
Voltage - Maximum	250V

Physical

Breakaway	No
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Black

Durability (mating cycles max)	100
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Resin	Polyester
Net Weight	0.310/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Tube
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	No
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

Mates With / Use With

Mates with Part(s)

Description	Part Number
Picoflex PF-50 Low Profile IDT Receptacles	<u>90327</u>