
Part Number : 1200060563
Product Description : Micro-Change (M12) Single-Ended Cordset, 4 Poles, Male (Straight) to Pigtail, 0.34mm² Black PVC Cable, 10.0m (32.81') Length
Series Number : 120006
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Number : 804006E03M100



Documents & Resources

Drawings

Drawing_1200060563_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead; Lead monoxide per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120006
Description	Micro-Change (M12) Single-Ended Cordset, 4 Poles, Male (Straight) to Pigtail, 0.34mm^2 Black PVC Cable, 10.0m (32.81') Length
IP Rating	IP67
Product Family	Brad Micro-Change (M12) Connectors
Product Name	Micro-Change (M12)
Protocol	N/A
Region	Europe
Type	Single Ended
UPC	883906068011

Agency

UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V

Physical

Cable Diameter	5.40mm (.213")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Black
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
Coupling Style	Threaded

Gender	Male-Pigtail
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	449.188/g
Orientation	Straight to Pigtail
Poles	4
Temperature Range - Operating	-30° TO +80°C
Wire/Cable Type	UL 2464
Wire Size (AWG)	22