



Part Number : [1200798013](#)
Product Description : Ultra-Lock (M12) Single-Ended Cordset, 4 Poles, Female (90°) to Pigtail, 22 AWG, PUR Cable, 2.0m (6.56') Length
Series Number : 120079
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Number : W04001P03M020



Documents & Resources

Drawings
[Drawing 1200798013_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

EU RoHS Certificate of Compliance

ZZCERT_CE - Declaration of Conformity : CER_4000408919_00_000.pdf

ZZCERT_UKCA - Declaration of Conformity : CER_4000410293_00_000.pdf

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120079
Description	Ultra-Lock (M12) Single-Ended Cordset, 4 Poles, Female (90°) to Pigtail, 22 AWG, PUR Cable, 2.0m (6.56') Length
IP Rating	IP69K
Product Family	Brad Ultra-Lock Connection System
Product Name	Ultra-Lock (M12)
Protocol	EtherNet
Region	Europe
Type	Single Ended
UPC	883906718756

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Cable Diameter	5.30mm (.209")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Black
Connector End A	Ultra-Lock (M12)
Connector End B	Pigtail
Coupling Style	Push to Lock
Gender	Female-Pigtail
Keyway	Single
LED Indicator	No

Material - Cable Jacket	PUR/PVC
Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Orientation	90° to Pigtail
Poles	4
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	EU Cable
Wire Size (AWG)	22