



Part Number : [1200720061](#)
Product Description : Micro-Change (1/2"-20 UNF) Single-Ended Cordset, 2 Poles, Female (Straight) to Pigtail, 22 AWG, PVC Cable, 1.83m (6.0') Length
Series Number : 120072
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Number : 702000D02F060



Documents & Resources

Drawings
[Drawing 1200720061_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

ZZCERT_CE - Declaration of Conformity : CER_4000408919_00_000.pdf

ZZCERT_UKCA - Declaration of Conformity : CER_4000410293_00_000.pdf

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120072
Description	Micro-Change (1/2"-20 UNF) Single-Ended Cordset, 2 Poles, Female (Straight) to Pigtail, 22 AWG, PVC Cable, 1.83m (6.0') Length
IP Rating	IP67
Product Family	Brad Micro-Change (M12) Connectors
Product Name	Micro-Change (1/2" - 20 UNF)
Protocol	PROFIBUS
Region	America
Type	Single Ended
UPC	78678875903

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Cable Diameter	5.72mm (.225")
Cable Length	1.83m (6.0')
Color - Cable Jacket	Yellow
Connector End A	Micro-Change (1/2" - 20 UNF)
Connector End B	Pigtail
Coupling Style	Threaded

Gender	Female-Pigtail
Keyway	Dual
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Contact	Copper Alloy
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - O-Ring	Nitrile Rubber
Material - Plating Mating	Gold
Net Weight	65.650/g
Orientation	Straight to Pigtail
Poles	2
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	UL 2661
Wire Size (AWG)	22