




Part Number : [901522310](#)
Product Description : 2.54mm Pitch C-Grid III
PC Board Connector, Dual Row, Right-Angle,
Straight PCB Pins 0.76µm Gold (Au) Selective,
10 Circuits
Series Number : 90152
Status : Active
Product Category : PCB Headers and
Receptacles



Documents & Resources

Drawings
[Drawing 901522310_sd.pdf](#)
[Packaging Design Drawing PK-90152-001-001.pdf](#)

3D Models and Design Files
[3D Model 901522310_stp.zip](#)

Specifications
[Application Specification 901190001-AS-000.pdf](#)
[Product Specification PS-99020-0001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	90152
Description	2.54mm Pitch C-Grid III PC Board Connector, Dual Row, Right-Angle, Straight PCB Pins 0.76µm Gold (Au) Selective, 10 Circuits
Application	Board-to-Board, Signal
Component Type	PCB Receptacle
Product Family	C-Grid Connector Products
Product Name	C-Grid III
UPC	800753671461

Agency

CSA	LR19980
-----	---------

Electrical

Current - Maximum per Contact	3.0A
Grounding to PCB	No
Voltage - Maximum	350V

Physical

Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	Black
Glow-Wire Capable	No
Guide to Mating Part	No

Keying to Mating Part	None
Lock to Mating Part	No
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	1.023/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Tube
PC Tail Length	2.90mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Plating min - Mating	0.762µm
Plating min - Termination	3.048µm
Polarized to PCB	No
Temperature Range - Operating	-55° to +125°C
Termination Interface Style	Through Hole

Solder Process Data

Lead-Free Process Capability	WAVE
------------------------------	------

Mates With / Use With

Mates with Part(s)

Description	Part Number
C-Grid III Right-Angle Dual Row Headers	<u>90122</u>
C-Grid III Vertical Dual Row Headers	<u>90131</u>