




Part Number : [930711001](#)
Product Description : 5.00mm Pitch Appli-
Mate RAST 2.5 Header, Vertical, 3 Circuits,
Reference K00, Glow-Wire Capable
Series Number : 93071
Status : Active
Product Category : PCB Headers and
Receptacles



Documents & Resources

Drawings
[Drawing 930711001_sd.pdf](#)

3D Models and Design Files
[3D Model 930711001_stp.zip](#)

Specifications
[Packaging Specification PK-90871-001-001.pdf](#)
[Packaging Specification PK-93070-001-001.pdf](#)
[Product Specification PS-93070-001-001.pdf](#)
[Product Specification PS-99020-0040-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	93071
Description	5.00mm Pitch Appli-Mate RAST 2.5 Header, Vertical, 3 Circuits, Reference K00, Glow-Wire Capable
Application	Power, Wire-to-Board
Comments	This Molex product is manufactured from material that has the following ratings, tested by independent agencies: a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12 and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s). If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options.
Component Type	PCB Header
Product Family	RAST Connector System
Product Name	RAST 2.5

UPC	883906320843
-----	--------------

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	6.0A
Voltage - Maximum	250V

Physical

Breakaway	No
Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Natural
Durability (mating cycles max)	10
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	Yes
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1.310/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Carton
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.50mm
Pitch - Mating Interface	5.00mm
Plating min - Mating	3.048µm

Plating min - Termination	3.048μm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-20° to +120°C
Termination Interface Style	Through Hole

Mates With / Use With

Mates with Part(s)

Description	Part Number
Appli-Mate RAST Power IDT Housings	<u>91627</u>
5.00mm Pitch Appli-Mate RAST 2.5 IDT Housings	<u>91717</u>
5.00mm Pitch Appli-Mate RAST 2.5 Female Connectors	<u>93051</u>

Use with Part(s)

Description	Part Number
Use With	RAST Standard Interface

Application Tooling

Global

Description	Part Number
RAST 2.5 and R-Power Semi-Automatic IDC Machine	<u>2166580100</u>