



Part Number : [1200980089](#)
Product Description : Micro-Change (M12)
Single-Ended Cordset, 5 Poles, Female
(Straight) to Pigtail, 24 AWG, 10.0m (32.81')
Length, PROFIBUS PUR Cable Preferred
Version in Europe
Series Number : 120098
Status : Active
Product Category : Circular Industrial
Cordsets
Engineering Number : B05S00PP4M100



Documents & Resources

Drawings
[Drawing 1200980089_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead; Lead monoxide per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

EU RoHS Certificate of Compliance

ZZCERT_CE - Declaration of Conformity : CER_4000406213_00_000.pdf

ZZCERT_UKCA - Declaration of Conformity : CER_4000410537_00_000.pdf

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120098
Description	Micro-Change (M12) Single-Ended Cordset, 5 Poles, Female (Straight) to Pigtail, 24 AWG, 10.0m (32.81') Length, PROFIBUS PUR Cable Preferred Version in Europe
IP Rating	IP67
Product Family	Brad Micro-Change (M12) Connectors
Product Name	Micro-Change (M12)
Protocol	EtherNet
Region	America
Type	Single Ended
UPC	78678852055

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V AC/DC

Physical

Cable Diameter	8.00mm (.315")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Violet
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Reverse

LED Indicator	No
Material - Cable Jacket	PUR
Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	777.008/g
Orientation	Straight to Pigtail
Poles	5
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	Twisted Pair
Wire Size (AWG)	24