




Part Number : [1300480062](#)
Product Description : Micro-Change (M12)
Single-Ended Cordset, 4 Poles, Male (90°) to
Pigtail, 24 AWG PVC Cable, 1.0m (3.28')
Length
Series Number : 130048
Status : Active
Product Category : Circular Industrial
Cordsets
Engineering Number : E10A00703M010



Documents & Resources

Drawings
[Drawing 1300480062_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per per ED/108/2014 (17 Dec 2014)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

ZZCERT_CE - Declaration of Conformity : CER_4000410151_00_000.pdf

ZZCERT_UKCA - Declaration of Conformity : CER_4000410546_00_000.pdf

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	130048
Description	Micro-Change (M12) Single-Ended Cordset, 4 Poles, Male (90°) to Pigtail, 24 AWG PVC Cable, 1.0m (3.28') Length
IP Rating	IP67
Performance Category	5e
Product Family	Brad Industrial Ethernet Solutions
Product Name	Micro-Change (M12)
Protocol	N/A
Region	America, Asia, Europe
Type	Single Ended
UPC	78678803920

Agency

UL	E200650
----	---------

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	30V

Physical

Cable Diameter	5.59mm (.220")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Teal
Connector End A	Micro-Change (M12)

Connector End B	Pigtail
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	D-coded
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Orientation	90° to Pigtail
Poles	4
Temperature Range - Operating	-20° to +75°C
Wire/Cable Type	N/A
Wire Size (AWG)	24