



Part Number : [1212100042](#)
Product Description : mPm DIN Valve Connector, Form C-8mm, External Threads, 2 Pole Plus Ground with C4 Circuit, 24V, Amber LED, Transparent, Nitrile Gasket
Series Number : 121210
Status : Active
Product Category : Circular Industrial Connectors
Engineering Number : S25200TC4H0T



Documents & Resources

Drawings
[Drawing 1212100042_sd.pdf](#)

Specifications
[Packaging Specification PK-121210-S25-001.pdf](#)
[STR-1299-001.pdf](#)
[Product Specification STR-1251-001.pdf](#)
[Product Specification PS-121201-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

ZZCERT_CE - Declaration of Conformity : CER_4000446150_00_000.pdf

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	121210
Description	mPm DIN Valve Connector, Form C-8mm, External Threads, 2 Pole Plus Ground with C4 Circuit, 24V, Amber LED, Transparent, Nitrile Gasket
IP Rating	IP65, IP67
Product Family	mPm DIN Valve Connectors
Product Name	mPm
Type	Field Attachable Connector
UPC	884982538856

Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	24V

Physical

Cable Diameter	N/A
Coupling Type	External Thread
Diagnostics / LEDs	Yes
Diagnostics Port	No
Form	C - 8mm
Gender	N/A
Keyway	None
Material - Connector Body	Polyamide
Material - Contact	Brass

Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Net Weight	1.000/g
Orientation	90° Angle
Pitch - Mating Interface	8.00mm
Poles	2
Temperature Range - Operating	-40°C to +90°C
Wire Size (AWG)	N/A

This document was generated on Sep 26, 2023