



Part Number : [1212110042](#)
Product Description : mPm DIN Valve Connector, Form C-Micro 9.4mm, External Threads, 2 Pole Plus Ground with C4 Circuit, 24V, Amber LED, Transparent, Nitrile Gasket
Series Number : 121211
Status : Active
Product Category : Circular Industrial Connectors
Engineering Number : S29200TC4H0T



Documents & Resources

Drawings
[Drawing 1212110042_sd.pdf](#)

Specifications
[Packaging Specification PK-121211-S29-001.pdf](#)
[STR-1299-001.pdf](#)
[Product Specification STR-1251-001.pdf](#)
[Product Specification PS-121201-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)
- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

ZZCERT_CE - Declaration of Conformity : CER_4000446152_00_000.pdf

ZZCERT_UKCA - Declaration of Conformity : CER_4000446168_00_000.pdf

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	121211
Description	mPm DIN Valve Connector, Form C-Micro 9.4mm, External Threads, 2 Pole Plus Ground with C4 Circuit, 24V, Amber LED, Transparent, Nitrile Gasket
IP Rating	IP65, IP67
Product Family	mPm DIN Valve Connectors
Product Name	mPm
Type	Field Attachable Connector
UPC	884982530942

Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	24V

Physical

Cable Diameter	N/A
Coupling Type	External Thread
Diagnostics / LEDs	Yes
Diagnostics Port	No
Form	C - Micro 9.4mm
Gender	N/A
Keyway	None

Material - Connector Body	Polyamide
Material - Contact	Brass
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Net Weight	15.103/g
Orientation	90° Angle
Pitch - Mating Interface	9.40mm
Poles	2
Temperature Range - Operating	-40°C to +90°C
Wire Size (AWG)	N/A

This document was generated on Sep 26, 2023