



Part Number : [1300080316](#)
Product Description : Mini-Change C-Size Single-Ended Cordset, 19 Poles, Female (90°) to Pigtail, 18 and 22 AWG, Black PUR Cable, 10.0m (32.81') Length
Series Number : 130008
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Number : 303001P80M100



Documents & Resources

Drawings
[Drawing 1300080316_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	130008
Description	Mini-Change C-Size Single-Ended Cordset, 19 Poles, Female (90°) to Pigtail, 18 and 22 AWG, Black PUR Cable, 10.0m (32.81') Length
IP Rating	IP67
Product Family	Brad Mini-Change Connectors
Product Name	Mini-Change
Protocol	DeviceNet
Region	Europe
Type	Single Ended
UPC	78678853541

Electrical

Current - Maximum per Contact	2.0A, 3.0A
Voltage - Maximum	300V AC/DC

Physical

Cable Diameter	11.43mm (.450")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Black
Connector End A	Mini-Change
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PUR
Material - Connector Body	TPE

Material - Contact	Copper Alloy
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Net Weight	1909.622/g
Orientation	90° to Pigtail
Poles	19
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	N/A
Wire Size (AWG)	18, 22

This document was generated on Sep 26, 2023