



Part Number : [1301460137](#)

Product Description : Watertite Extreme Receptacle with Single Flip Coverplate, 2 Pole/3 Wire, NEMA 6-15, 250V

Series Number : 130146

Status : Active

Product Category : Wiring Devices

Engineering Number : 60W49



---

## Documents & Resources

### Drawings

[Drawing 1301460137\\_sd.pdf](#)

### 3D Models and Design Files

[3D Model 1301460137\\_stp.zip](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Not Reviewed per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474

- chemSHERPA (xml)

EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Wiring Devices
Series	130146
Description	Watertite Extreme Receptacle with Single Flip Coverplate, 2 Pole/3 Wire, NEMA 6-15, 250V
IP Rating	IP67
NEMA Configuration	NEMA 6-15
Product Family	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite Extreme
Specialty	N/A
Type	Receptacle
UPC	78678871403

### Agency

CSA	LR6837
UL	E68122

### Electrical

Current - Maximum per Contact	15.0A
GFCI	No
Voltage - Maximum	250V

### Physical

Cord Type	N/A
Flange	No
Flip Lid	Yes
Gender	Female
Length	N/A

Lighted Connector	No
Locking Blade	No
Poles	2-pole/3-wire
Receptacle Type	Single

---

This document was generated on Sep 26, 2023