




Part Number : [1718130005](#)
Product Description : 3.96mm Pitch, KK 396
RPC Vertical Header with Friction Lock, Tin
(Sn) Plating, Pin Length 17.02mm, Bag, 5
Circuits, without Pegs
Series Number : 171813
Status : Active
Product Category : PCB Headers and
Receptacles



Documents & Resources

Drawings
[Drawing 1718130005_sd.pdf](#)
[Packaging Design Drawing PK-41791-001-001.pdf](#)

3D Models and Design Files
[3D Model 1718130005_stp.zip](#)
[Symbol Footprint Data SYM-171813-0005-001.zip](#)

Specifications
[Product Specification PS-171813-0001-001.pdf](#)
[Product Specification PS-171813-0002-001.pdf](#)
[Test Summary TS-171813-0001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	171813
Description	3.96mm Pitch, KK 396 RPC Vertical Header with Friction Lock, Tin (Sn) Plating, Pin Length 17.02mm, Bag, 5 Circuits, without Pegs
Application	Board-to-Board, Power, Signal, Wire-to-Board
Comments	See Product Specification for maximum current rating by material, AWG, and orientation; See Product Specification for operating temperature range by material.
Component Type	PCB Header
Product Family	KK Interconnect Systems
Product Name	KK 396
UPC	887191375328

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	5.0A, 7.0A
Voltage - Maximum	250V

Physical

Breakaway	No
-----------	----

Circuits (Loaded)	5
Circuits (maximum)	5
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Flammability	94V-2
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Matte Tin
Material - Plating Termination	Matte Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	1.585/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Bag
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	3.96mm
Plating min - Mating	1.524µm
Plating min - Termination	1.524µm
Polarized to Mating Part	Yes
Shrouded	Partial
Stackable	No
Temperature Range - Operating	-40° to +105°C, -40° to +80°C
Termination Interface Style	Through Hole

Solder Process Data

Max-Duration	30
Lead-Free Process Capability	SMC&WAVE
Max-Cycle	3
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
KK 3.96mm Single Row Crimp Housings	<u>2139</u>
KK 3.96mm Single Row Crimp Housings	<u>3069</u>
KK 3.96mm Crimp Housings	<u>41695</u>
KK 396 PC Board Connector	<u>41815</u>
KK 3.96mm Pitch Single Row Crimp Housings	<u>6442</u>