



**Part Number :** [2043130018](#)  
**Product Description :** Centrality 3.40mm Top-entry, Knurled Press-fit Socket Assembly with +/-1.00mm Self-alignment Capability in Tray  
**Series Number :** [204313](#)  
**Status :** Active  
**Product Category :** PCB Headers and Receptacles



## Documents & Resources

### Drawings

[Drawing 2043130018\\_sd.pdf](#)  
[Packaging Design Drawing 2043130018-PK-000.pdf](#)

### 3D Models and Design Files


[3D Model 2043130018\\_stp.zip](#)

### Specifications

[Application Specification 2043130018-AS-000.pdf](#)  
[Product Specification 2043130018-PS-000.pdf](#)  
[Test Summary 2043130018-TS-000.pdf](#)  
[Test Summary 2043131234-TS-000.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

## Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	PCB Headers and Receptacles
Series	204313
Description	Sentrality 3.40mm Top-entry, Knurled Press-fit Socket Assembly with +/-1.00mm Self-alignment Capability in Tray
Application	Busbar-to-Board, Busbar-to-Busbar, Power
Comments	Current and voltage performances are dependent upon application variables.
Component Type	PCB Receptacle
Product Family	Sentrality Pin and Socket Interconnect System
Product Name	Sentrality
UPC	191130148998

#### Electrical

Current - Maximum per Contact	75.0A
Voltage - Maximum	600V

#### Physical

Circuits (Loaded)	1
Circuits (maximum)	1
Diameter	3.40mm
Durability (mating cycles max)	200
Glow-Wire Capable	No

Guide to Mating Part	Yes
Height Above Board	3.40mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Silver
Mating Orientation	Top-entry
Net Weight	8.056/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Tray
PCB Retention	None
Pitch - Mating Interface	N/A
Polarized to PCB	No
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Press-Fit

#### Solder Process Data

Max-Duration	600
Lead-Free Process Capability	SMC&WAVE
Max-Cycle	2
Max-Temp	205

---

#### Mates With / Use With

##### Mates with Part(s)

Description	Part Number
Sentrality Pins	<u>203263</u>