




Part Number : [5046940600](#)
Product Description : CP-3.3 Plug Housing,
3.30mm Pitch, Single Row, Polarized, Positive
Inertia Lock, 6 Circuits, Natural
Series Number : 504694
Status : Active
Product Category : Connector Housings



Documents & Resources

Drawings

[Drawing 5047406100_sd.pdf](#)

3D Models and Design Files

[3D Model 5047406100_stp.zip](#)

Specifications

[Application Specification AS-504740-001-001.pdf](#)

[Packaging Specification 5047409200-200.pdf](#)

[Product Specification PS-504740-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	FFC / FPC Connectors
Series	504740
Description	0.30mm Pitch Easy-On Back Flip FPC Connector, Right-Angle, Surface Mount, Dual Contact Style, 0.95mm Height, 61 Circuits
Product Family	Easy-On FFC FPC Connectors
Product Name	Easy-On
UPC	887191502151

Electrical

Current - Maximum per Contact	0.3A
Voltage - Maximum	50V

Physical

Actuator Type	Back Flip
Circuits (Loaded)	61
Color - Resin	Black
Contact Position	Dual
Durability (mating cycles max)	10
Mated Height	0.95mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer
Net Weight	114.317/mg
Number of Rows	1

Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Mounting	Surface Mount
PCB Retention	Yes
Pitch - Mating Interface	0.30mm
Pitch - Termination Interface	0.30mm
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire/Cable Type	FPC only