



Part Number : [1200678461](#)
Product Description : Micro-Change (M12) Single-Ended Cordset with Knurled Hexnut and PNP LED Sensors, 4 Poles, Female (90°) to Pigtail, 22 AWG, Unshielded WSOR Cable, 5.0m (16.40') Length
Series Number : 120067
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Number : 8040P1B30M050



Documents & Resources

Drawings
[Drawing 1200678461_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120067
Description	Micro-Change (M12) Single-Ended Cordset with Knurled Hexnut and PNP LED Sensors, 4 Poles, Female (90°) to Pigtail, 22 AWG, Unshielded WSOR Cable, 5.0m (16.40') Length
IP Rating	IP67
Product Family	Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable
Product Name	Micro-Change (M12)
Protocol	N/A
Region	Europe
Type	Single Ended
UPC	889056091374

Agency

UL	E152210
----	---------

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	10-30V DC

Physical

Cable Diameter	5.10mm (.201")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
Coupling Style	Knurled Hexnut, Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	PNP Sensors

Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Orientation	90° to Pigtail
Poles	4
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	WSOR
Wire Size (AWG)	22