




Part Number : [1300478009](#)
Product Description : Brad RJ-45 Field Attachable Connector, 8 Poles, Right-Angle, Male, Shielded, IDC Termination, AWG 24-22
Series Number : 130047
Status : Active
Product Category : Circular Industrial Connectors
Engineering Number : E6AS07-5



Documents & Resources

Drawings
[Drawing 1300478009_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2020)9139-DC (19 Jan 2021)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

EU RoHS Certificate of Compliance

ZZCERT_CE - Declaration of Conformity : CER_4000409980_00_000.pdf

ZZCERT_UKCA - Declaration of Conformity : CER_4000410293_00_000.pdf

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	130047
Description	Brad RJ-45 Field Attachable Connector, 8 Poles, Right-Angle, Male, Shielded, IDC Termination, AWG 24-22
Approvals	cCSAus certified
Comments	POE+ according to IEEE 802.3AT
IP Rating	IP20
Product Family	Brad Industrial Ethernet Solutions
Product Name	RJ45 Cat6A
Type	Field Attachable Connector
UPC	889056622820

Agency

UL	E361772
----	---------

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	48V

Physical

Cable Diameter	5.50-10.00mm (.216-.393")
Communication Speed	10-Gigabit Ethernet
Coupling Type	Push to Lock
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male

Keyway	X-coded
Material - Connector Body	Zinc Die-Cast with Nickel
Material - Contact	Brass
Material - Coupling Nut	Clear UL 94 V0
Material - Plating Mating	Gold
Net Weight	22.582/g
Orientation	90° Angle
Poles	8
Temperature Range - Operating	-40°C to +85°C
Wire Size (AWG)	24-22/1

This document was generated on Sep 26, 2023