



Part Number : [2018421030](#)
Product Description : MultiCat High-Power Vertical Header, 3 Circuits, Key A, Black
Series Number : 201842
Status : Active
Product Category : PCB Headers and Receptacles
Engineering Number : 2018421030-FCT



Documents & Resources

Drawings

[Drawing 2018421030_sd.pdf](#)
[Packaging Design Drawing 2018420000-PK-000.pdf](#)

3D Models and Design Files

[3D Model 2018421030_stp.zip](#)

Specifications

[Application Specification 2018400000-AS-000.pdf](#)
[Product Specification 2018400000-PS-000.pdf](#)
[Test Summary 2018400000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

[Multiple Part Product Compliance Statements](#)
- Eu RoHS

- REACH SVHC

- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D

- Molex Product Compliance Declaration

- IEC-62474

- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	201842
Description	MultiCat High-Power Vertical Header, 3 Circuits, Key A, Black
Application	Power, Wire-to-Board
Component Type	PCB Header
Product Family	MultiCat Power Connectors with Precision-Machined Contacts
Product Name	MultiCat
UPC	889056747691

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	40.0A
Voltage - Maximum	1000V AC/DC

Physical

Breakaway	No
Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Black

Durability (mating cycles max)	500
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	PEI
Net Weight	8.315/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Tray
PCB Thickness - Recommended	2.50mm
Pitch - Mating Interface	7.40mm
Plating min - Mating	0.102µm
Plating min - Termination	5.080µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Temperature Range - Operating	-40° to +150°C
Termination Interface Style	Through Hole

Mates With / Use With

Mates with Part(s)

Description	Part Number
MultiCat-to-MultiCat High-Power Off-the-Shelf (OTS) Cable Assembly, Female, Single Row, 300.00mm Length, 8 AWG, 3 Circuits, Key A, Black	<u>0451410301</u>
MultiCat-to-MultiCat High-Power Off-the-Shelf (OTS) Cable Assembly, Female, Single Row, 1.0m Length, 8 AWG, 3 Circuits, Key A, Black	<u>0451410310</u>

MultiCat High-Power Inline Receptacle Housings	<u>201841</u>
---	---------------