



Part Number : [1200910028](#)
Product Description : Nano-Change (M8) Field Attachable Connector, 3 Poles, Straight, Female, Unshielded, IDC Termination, Cable Diameter 2.50-5.20mm
Series Number : 120091
Status : Active
Product Category : Circular Industrial Connectors
Engineering Number : N03FA03144



Documents & Resources

Drawings
[Drawing 1200910028_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per ED/30/2017 (7 July 2017)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

EU RoHS Certificate of Compliance

ZZCERT_CE - Declaration of Conformity : CER_4000408919_00_000.pdf

ZZCERT_UKCA - Declaration of Conformity : CER_4000410293_00_000.pdf

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	120091
Description	Nano-Change (M8) Field Attachable Connector, 3 Poles, Straight, Female, Unshielded, IDC Termination, Cable Diameter 2.50-5.20mm
Approvals	cCSAus certified
IP Rating	IP67
Product Family	Brad Nano-Change (M8) Products
Product Name	Nano-Change (M8)
Type	Field Attachable Connector
UPC	889056508452

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	60V

Physical

Cable Diameter	2.50-5.20mm (.098-.205")
Coupling Type	Internal Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Female
Keyway	None
Material - Connector Body	PA
Material - Contact	Copper Alloy
Material - Coupling Nut	Zinc Die-Cast, Nickel-Plated

Material - Plating Mating	Gold
Net Weight	66.000/g
Orientation	Straight
Poles	3
Temperature Range - Operating	-25°C to +80°C
Wire Size (AWG)	20-24

Mates With / Use With

Mates with Part(s)

Description	Part Number
Nano-Change (M8) Field Attachable Connector, 3 Poles, Straight, Male, Unshielded, IDC Termination, Cable Diameter 2.50-5.20mm	<u>1200910027</u>