

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Identification on the label/Trade name

label designation/Name of product

Kabelgel Cable Scout+

Product-no.: 897-90031

1.2 Relevant identified uses of the substance or mixture and uses advised against

No data available

1.3 Details of the supplier of the safety data sheet

Supplier

HellermannTyton GmbH

Großer Moorweg 45

Germany-25436 Tornesch

P.O. Box: 2151

Germany-25437 Tornesch

Telephone: +49-(0)4122-701-0

Telefax: +49-(0)4122-701-400

E-mail: msds@hellermannntyton.de

Dept. responsible for information: Safety and Environmental Management

Information telephone: +49-(0)4122-701-0

Information telefax: +49-(0)4122-701-400

www.HellermannTyton.de

1.4 Emergency telephone number

Health and Safety Executive (HSE) Chemicals Regulation Directorate, Telephone: +44 151 951 3317

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008 [CLP]

remark

This mixture is classified as not hazardous according to regulation (EC) No 1272/2008 [CLP].

2.2 Label elements

No data available

2.3 Other hazards

No data available

SECTION 3: Composition / information on ingredients

remark

Full text of R-, H- and EUH-phrases: see section 16.

3.1/3.2 Substances/Mixtures

Description

Lubricant

Hazardous ingredients

2-methyl-2H-isothiazol-3-one

<=0,1 %

CAS 2682-20-4

EC 220-239-6

Acute Tox. 3, H301 / Acute Tox. 3, H311 / Acute Tox. 2, H330 / Skin

Corr. 1B, H314 / Aquatic Acute 1, H400 / Skin Sens. 1, H317 / STOT

SE 3, H335

SECTION 4: First aid measures

4.1 Description of first aid measures

Following skin contact

Wash immediately with:
Water and soap

After eye contact

Rinse immediately carefully and thoroughly with eye-bath or water.

After ingestion

Rinse mouth thoroughly with water.

4.2 Most important symptoms and effects, both acute and delayed

No data available

4.3 Indication of any immediate medical attention and special treatment needed

No data available

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media

Foam
Dry extinguishing powder
Carbon dioxide (CO₂)
Water spray

5.2 Special hazards arising from the substance or mixture

No data available

5.3 Advice for firefighters

No data available

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

No data available

6.2 Environmental precautions

Do not allow to enter into surface water or drains.

6.3 Methods and material for containment and cleaning up

For containment

Suitable material for taking up:

Pick up mechanically.

6.4 Reference to other sections

Safe handling: see section 7
Disposal: see section 13
Personal protection equipment: see section 8

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Protective measures

Measures to prevent fire

Keep away from sources of ignition. - No smoking.

Environmental precautions

Shafts and sewers must be protected from entry of the product.

7.2 Conditions for safe storage, including any incompatibilities

Hints on joint storage

Materials to avoid

Do not store together with:
Oxidising agent

Further information on storage conditions

Protect against:

Heat
Frost
UV-radiation/sunlight

storage temperature >0 - <20 °C

7.3 Specific end use(s)

No data available

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

No data available

8.2 Exposure controls

Personal protection equipment

Eye/face protection

Suitable eye protection:

Eye glasses with side protection

Skin protection

Suitable gloves type:

Gloves with long cuffs
in accordance with standard EN 374

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Appearance

Physical state

Gel

Colour

According to product specification

Odour

characteristic

| parameter | Method - source - remark |
|---|--------------------------|
| pH | not determined |
| Melting point/freezing point | not determined |
| Initial boiling point and boiling range | not determined |
| Flash point (°C) | not determined |
| Evaporation rate | not determined |
| flammability | not determined |
| Upper explosion limit | not determined |

| parameter | Method - source - remark |
|--|--------------------------|
| lower explosion limit | not determined |
| Vapour pressure | not determined |
| Vapour density | not determined |
| Density | not determined |
| Fat solubility (g/L) | not determined |
| Water solubility (g/L) | not determined |
| Soluble (g/L) in | not determined |
| Partition coefficient: n-octanol/water | not determined |
| Auto-ignition temperature | not determined |
| Decomposition temperature | not determined |

9.2 Other safety information

No data available

SECTION 10: Stability and reactivity

10.1 Reactivity

No information available.

10.2 Chemical stability

No information available.

10.3 Possibility of hazardous reactions

No information available.

10.4 Conditions to avoid

No information available.

10.5 Incompatible materials

Materials to avoid

Oxidising agent, strong

10.6 Hazardous decomposition products

No information available.

SECTION 11: Toxicological information

11.1 Information on toxicological effects

No information available.

SECTION 12: Ecological information

12.1 Toxicity

No information available.

12.2 Persistence and degradability

No information available.

12.3 Bioaccumulative potential

No information available.

12.4 Mobility in soil

No information available.

12.5 Results of PBT and vPvB assessment

This substance does not meet the PBT/vPvB criteria of REACH, annex XIII.

12.6 Other adverse effects

No information available.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Appropriate disposal / Product

Waste disposal according to official state regulations.

Appropriate disposal / Package

Handle contaminated packages in the same way as the substance itself.

Waste code product 070000

hazardous waste No

Waste name

WASTES FROM ORGANIC CHEMICAL PROCESSES

Waste code product 070600

hazardous waste No

Waste name

wastes from the MFSU of fats, grease, soaps, detergents, disinfectants and cosmetics

Waste code product 070699

hazardous waste No

Waste name

wastes not otherwise specified

SECTION 14: Transport information

| | Land transport (ADR/RID) | Sea transport (IMDG) | Air transport (ICAO-TI / IATA-DGR) |
|---|--------------------------|----------------------|------------------------------------|
| 14.1 UN-No. | not applicable | not applicable | not applicable |
| 14.2 Proper Shipping Name | | | |
| 14.3 Class(es) | | | |
| 14.4 Packing group | | | |
| 14.5 ENVIRONMENTALLY HAZARDOUS | | | |
| 14.6 Special precautions for user | | | |
| 14.7 Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code | | | |

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

15.2 Chemical Safety Assessment

No data available

SECTION 16: Other information

Abbreviations and acronyms

For abbreviations and acronyms, see: ECHA Guidance on information requirements and chemical safety assessment, chapter R.20 (Table of terms and abbreviations).

Relevant R-, H- and EUH-phrases (Number and full text)

H301, R25 Toxic if swallowed.

H311, R24 Toxic in contact with skin.

H314 Causes severe skin burns and eye damage.

H317 May cause an allergic skin reaction.

H330 Fatal if inhaled.

H335 May cause respiratory irritation.

H400 Very toxic to aquatic life.