

## Eco-V Handheld Thermal Camera



The handheld thermal camera is based on the thermal technology, specially designed for the needs of temperature measuring applications. People can quickly troubleshoot faults on-site.

### Key Feature

- Thermal resolution: 96 × 96 (9,216 pixels)
- 112:1 Distance to spot ratio (D:S)
- SuperIR: 240 × 240 (57,600 pixels)
- NETD: < 50 mK (@ 25°C, F# = 1.0)
- Measurement presets: center spot, hot spot, cold spot, off
- 25 Hz image frequency
- Laser pointer
- Built-in 4 GB flash memory: 30,000 pictures
- Up to 8 hours continuous running
- Thermal/Visual/Fusion


## ▪ Specification

<b>Infrared Image</b>	
IR Resolution	96 × 96 (9,216 pixels)
SuperIR	240 × 240 (57,600 pixels)
Distance to Spot Ratio (D:S)	112:1
Image Frequency	25 Hz
NETD	< 50 mK (@ 25°C, F# = 1.0)
Detector Pitch	12 μm
Focal Length	1.35 mm
Spectral Range	7.5 to 14 μm
F-number	F1.0
Field of View (FOV)	50° × 50°
Spatial Resolution (IFOV)	8.89 mrad
Min. Focus Distance	0.1 m (0.33 ft)
Focus Mode	Focus Free
<b>Image Display</b>	
Display	240 × 320 Resolution, 2.4" LCD Screen
Image Modes	Thermal/Visual/Fusion
Color Palettes	White Hot, Black Hot, Rainbow, Ironbow, Red Hot, Fusion
Color Alarm	Above alarm
Visual Camera	640 × 480
<b>Measurement and Analysis</b>	
Object Temperature Range	-20°C to 550°C (-4°F to 1022°F)
Accuracy	Max (±2°C/3.6°F, ±2%) at ambient temperature 25°C (77°F) and object temperature above 0°C (32°F)
Measurement Tools	Center Spot, Hot Spot, Cold Spot
Level and Span Mode	Auto/Manual
<b>Data Storage and Communication</b>	
Storage Media	Built-in 4 GB flash memory
Image Storage Capacity	Approx. 30,000 Images
<b>General</b>	
USB Interface	USB Type-C
Laser	Yes, Class II
Battery Type	Rechargeable Li-ion battery
Battery Charging Time	Approx. 3 hours fully charged (Adapter Output: 5 V 2 A)
Battery Operating Time	Approx. 8 hours
Protection Level	IP54
Drop Test Height	2 m (6.56 ft)
Working Temperature Range	-10°C to 50°C (14°F to 122°F)
Storage Temperature Range	-40°C to 70°C (-40°F to 158°F)
Relative Humidity	< 95% non-condensing
Weight	Approx. 290 g (0.64 lb)
Dimension	196 × 117 × 59 mm (7.7" × 4.6" × 2.3")
Tripod Mounting	UNC ¼"-20

## ▪ Available Model

Eco-V

## ▪ Dimension



Unit: mm (inch)

## ▪ Accessory

### ▪ Optional



HM-B01-POUCH

COMPLIANCE NOTICE: The thermal series products might be subject to export controls in various countries or regions, including without limitation, the United States, European Union, United Kingdom and/or other member countries of the Wassenaar Arrangement. Please consult your professional legal or compliance expert or local government authorities for any necessary export license requirements if you intend to transfer, export, re-export the thermal series products between different countries.



 HIKMICRO Thermography  hikmicro\_thermography  HIKMICRO Thermography  HIKMICRO  info@hikmicrotech.com  http://hikmicrotech.com/en

© 2023 Hangzhou HIKMICRO Sensing Technology Co., Ltd. All Rights Reserved.  
Data subject to change without notice!