

VOLTCRAFT - RELIABLE AND PRECISE. SINCE 1982.

For more than 40 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.



LITHIUM BATTERY


Item No.:	Pcs per pack
2986444	1
2542832	4
3373186	40

TECHNICAL DATA

Type:	CR2450
Classification:	Non-rechargeable
Chemical system:	Lithium/Manganese Dioxide (Li/MnO ₂)
Nominal voltage:	3.0 V
Weight (approx.)	6.2 g
Capacity:	580 mAh
Loading:	7.5 kΩ (20 ±2 °C, 55 ±20 % RH)
Cut-off voltage:	2.0 V
Operating conditions:	-18 to +50 °C
Storage conditions:	0 to +30 °C, 55 ±20 % RH
Heavy metals:	No added mercury (Hg), Cadmium (Cd), or Lead (Pb)

For performance and safety, observe the operating / storage conditions. Capacity varies depending on the applied load, temperature, and cut-off voltage.

DIMENSIONS (mm)



Dimension	Min.	Max.
Ø	24.2	24.5
H	4.6	5.0



PERFORMANCE CHARACTERISTICS

Discharge

