## Datasheet



# Entac Solar Plastic Wall Lamp 15W SMD 3 head with removable Solar Panel

**Product code:** ESL3H-SMD-RS

**ID:** AB-190518 **Date of issue:** 2022-05-04

**Company name:** Armin Trade Kft.

Company address: Kossuth utca 22 2/4, 4024 Debrecen Page: 1/2

### **SPECIFICATIONS**

EAN code: 5999097988306

Warranty:

Built-in battery:

Color:

Material:

Packaging: 1/b 20/c

Certifications: CE

### **TECHNICAL DETAILS**

Wattage: 15W

Power source: Li-ion 2400mAh

Max. beam distance:

Working time:

Rechargeable:

IP standard: IP65

## **BOX PICTURE**



## **Datasheet**



## Entac Solar Plastic Wall Lamp 15W SMD 3 head with removable Solar Panel

**Product code:** ESL3H-SMD-RS

**ID:** AB-190518 **Date of issue:** 2022-05-04

**Company name:** Armin Trade Kft.

Company address: Kossuth utca 22 2/4, 4024 Debrecen Page: 2/2

### **PRODUCT SIZE**

Size:

### **CARDBOARD BOX**

EAN: 5999097988306

Packaging: 1/b 20/c

Dimensions: 191mm x 123mm x 124mm

Net weight: 600g Gross weight: 620g

### **CARTON**

EAN: 5999097988313

Packaging: 1/b 20/c

Dimensions: 650mm x 400mm x 270mm

Net weight: 12kg Gross weight: 12.4kg

### **PALLET EXAMPLE**

Height:

Width: 120cm (std Euro pallet)
Mepth: 80cm (std Euro pallet)

Cartons per pallet: 0carton/pallet

Cartons per row:

Net weight: 0.6kg
Gross weight: 0.62kg

### **PRODUCT PICTURE**

