


	Feature	Description	
Artwork	Dimensions	182*124*70mm	
	Weight	about 650g	
	Picture		
	Form factor	5G CPE(SA & NSA) Support: 5G NR CA 5G NR + LTE EN-DC	
	User manual		
	Quick guide		
	Warranty cards		
	Battery		
	AC adapter		
	Network cable	1 cable is included in the package	
	EAN		
	TAC		
	Solution	Wireless chipset supplier	Qualcomm
		Routing and WiFi chipset supplier	Qualcomm
	Wireless chipset model	SDX62	
	Wireless processor info	Arm Cortex-A7 up to 1.8 GHz	
	Routing and WiFi chipset model	WCN6856	
	SLIC		
	USIM/SIM slot	Standard 6PIN SIM card interface 3V SIM card and 1.8V SIM card	
	Memory(SDRAM/NAND)	8Gbits Nand+8Gbits LPDDR4	
	MICRO SD slot		
	USB interface	1	
	RJ45 interface	2	
	RJ11 interface	1	
	WiFi users access	64	
	Maximum power consumption	about 15w	
	Power indication LED	Single color (White) Always on(White)----power on Off----powered off	

	WiFi indication LED	Single color (White) Always on----WLAN working normally Blinking----WPS is activating
	Network mode indication LED	Red----Turn on but not register White Solid----Connect or Register to NSA or SA network Blue Solid----Connect or Register to 3G or LTE only
	WAN signal strength indication LED	3 LED (White) The stronger the signal strength is, the more LED light on
	LAN port LED	Single color (Green&Orange) Green Solid----The LAN port is connected Orange blink----The LAN port is connected with data transmission Off----No network cable connected
RF	Chipset	SDX62
	SRS	
	Waveform	CP-OFDM for UL&DL DFT-s-OFDM for UL
	Sub Carrier	30KHz, 15KHz
	Main antenna	Internal antenna
	Antenna Gain	700~960MHz: 1~1.5dbi 1450~2700MHz: 2~2.5dbi 3300~4200MHz: 4dBi and 9dBi
	GSM band	
	UMTS band	B1/8
	LTE band	B1/3/7/8/20/28/32/38/40/42/43
	5G Sub6 Band	N1/3/7/8/20/28/38/40/75/77/78
	5G mmWave Band	
	NSA 5G + LTE	Yes
	NR CA	Yes, just support 2CA
	MIMO for wireless	5G Sub6:n1,n3,n38,n40,n75,n78 supports 4*4MIMO; LTE: B1,B3,B32,B7,B38,B40 supports 4MIMO
	transmitter power for wireless	26dBm for N78 23dBm for other bands
	WiFi band	2.4G & 5G
	MIMO for WiFi	2*2 MIMO for both 2.4G&5G
	MU-MIMO	
Max. transmitter power for WiFi	17dBm for 2.4GHz 17.5dBm for 5GHz	
WCDMA	WCDMA CS: UL 64kbps/DL 64kbps WCDMA PS: UL 384kbps/DL 384kbps HSDPA: DL 14.4Mb/s(Category 10) DL 21Mb/s(Category 14) DL 42Mb/s(Category 24) HSUPA: UL 5.76Mb/s(Category 6)	
LTE	LTE FDD(DL Category19, UL Category18): DL 1.6Gb/s UL 200Mbps LTE TDD DL 1.12Gb/s UL 40Mb/s	
NSA 5G Sub + LTE Band	LTE FDD + Sub6G DL 2.716 Gb/s UL 280Mb/s	

Technical standard	SA 5G Sub6	5G Sub6G -TDD DL 1.716 Gb/s UL 160Mb/s	
	Bandwidth of Sub6G	40MHz, 60MHz, 80MHz, 100MHz, 50MHz, 90MHz	
	Modulation	Sub6G DL: 256QAM UL: 256QAM LTE DL:256QAM UL: 256QAM	
	BWP		
	Network Slicing		
	3GPP release	Release 16	
	WiFi standard	802.11b/g/n/a/ac/ax	
	WiFi Band	2.4G: 20M/40M 5G: 20M/40M/80M/160M	
	WiFi Speed	2.4GHz 2MIMO 575Mbps 5GHz 2MIMO 2.4Gbps The total speed can up to 2.975Gbps	
	WiFi security	WPA2-PSK	
	WPS	PBC(Push Button Config) & station PIN	
	IP protocols	RFC 791 (IP)	
		RFC 793 (TCP)	
		RFC 768 (UDP)	
		RFC 792 (ICMP)	
		RFC 826 (ARP)	
		RFC 1661 (PPP)	
		RFC 1332 (IPCP)	
		RFC 1334 (PAP)	
	RFC 1994 (CHAP)		
NAT/NAPT	RFC 3022		
Browser	IE		
	Firefox		
	Safari		
	Opera		
Chrome			
ZTE Link	Android and iOS APP to management the CPE		
Router	Port forwarding		
	IP filter		
	DMZ		
	UPnP		
	VPN passthrough	PP2P/L2TP/IPSec	
	VPN Client	PP2P/L2TP	
	Voice		
	Fax		
	SMS		
	MMS		
	Phonebook		
	Network lock		
	IPV4/IPV6		
	Language	English Default	
	Firewall switch	Enable/Disable IP/MAC/Port/URL filter	
	TR069		

	Online update	FOTA
HW buttons & switches	Power button	
	Reset button	To restore factory default configurations after pressing for 3 seconds
	WPS button	To activate the PBC(Push Button Config) function
Approvals & Certification	CE	
	ROHS	
	WEEE	
	GCF	
	FCC	
	WiFi certification	
	PTCRB	
	REACH	
	Operating temperature	-20 to 55° C
	Storage temperature	-40 to 70° C
	Humidity	5% to 95%
Market launch details	Engineering samples (yyyy/mm/dd)	30. Jan 22
	Final samples (yyyy/mm/dd)	30. Mrz 22
	Product market launch date (planned) (yyyy/mm/dd)	30. Apr 22

Support	Remarks
Yes	
Yes	
Optional	
Yes	
Optional	
No	
Yes	
Yes	
Optional	Can be customized
Optional	
	Power Management: PMX65
Yes	
	4FF
No	
Yes	TypeC 3.1 Only for debug
Yes	1GE: 10Base-T /100Base-T /1000Base-T
Yes	default: VoLTE&CSFB

	Show the better network mode signal strength.
	It's standard RJ45 LED status
Yes	N41, N77, N78, N79
Yes	
Yes	Support SCS 30KHz for TDD bands and 15KHz for FDD bands
No	
Yes	
Yes	
Yes	
No	Doesn't support mmWave by default.
Yes	There are so many EN-DC ability on this device, if you want to know more ability of this device to match your network, please provide your requirement and make further evaluation. When EN-DC is supported,, the max ability is: 10Layer LTE + 120M TDD Sub6(2CC); 16 Layer LTE + 80M TDD sub6(1CC)
No	
	FDD peak rates require DL: 256QAM + 5CA (16 layers) ; UL: 256QAM + 2CA intra-bands and inter-bands TDD peak rates require DL: 256QAM + 5CA (16 layers) ; UL: 256QAM + 2CA intra-bands and inter-bands. And TDD frame config 2 (DL/UL ratio 7:2)
	LTE FDD + Sub6G DL: LTE 10layer/256QAM + NR 120M /256QAM +75% DL duty cycle; UL: LTE 2CA/256QAM + NR 100M/256QAM +25% UL duty cycle;

