

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 29.09.2021

Version number 6 (replaces version 5)

Revision: 13.11.2019

SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- **Identification of the substance/preparation:** ESD Protect ESD-Oberflächenreiniger
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**
No further relevant information available.
- **Application of the substance / the mixture** Cleaning material/ Detergent
- **1.3 Details of the supplier of the safety data sheet**
- **Company/undertaking identification:**
ESD-Protect GmbH
Industriestraße 27
56276 Großmaischeid
Telefon: 02689-92870-0
E-Mail: info@esd-protect.de
- **Further information obtainable from:** Produktentwicklung
- **1.4 Emergency telephone number:**
Notfallauskunft: Der Notruf ist zu den üblichen Bürozeiten, werkstags zwischen 8 und 17 Uhr erreichbar, 02689 92780-0 (Diese Nummer ist nur zu den Bürozeiten besetzt)

SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**
The product is not classified, according to the CLP regulation.
- **2.2 Label elements**
- **Labelling according to Regulation (EC) No 1272/2008** Not applicable
- **Hazard pictograms** Not applicable
- **Signal word** Not applicable
- **Hazard statements** Not applicable
- **Additional information:**
EUH208 Contains reaction mass of: 5-chloro-2-methyl-4-isothiazolin-3-one [EC no. 247-500-7] and 2-methyl-2H-isothiazol-3-one [EC no. 220-239-6] (3:1). May produce an allergic reaction.
- **2.3 Other hazards**
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

SECTION 3: Composition/information on ingredients

- **3.2 Mixtures**
- **Description:** Mixture of substances listed below with nonhazardous additions.

Dangerous components:

CAS: 55965-84-9 Index number: 613-167-00-5	reaction mass of: 5-chloro-2-methyl-4-isothiazolin-3-one [EC no. 247-500-7] and 2-methyl-2H-isothiazol-3-one [EC no. 220-239-6] (3:1) ⚠ Acute Tox. 3, H301; Acute Tox. 2, H310; Acute Tox. 2, H330; ⚠ Skin Corr. 1C, H314; Eye Dam. 1, H318; ⚠ Aquatic Acute 1, H400 (M=100); Aquatic Chronic 1, H410 (M=100); ⚠ Skin Sens. 1A, H317 Specific concentration limits: Skin Corr. 1C; H314: C ≥ 0.6 % Skin Irrit. 2; H315: 0.06 % ≤ C < 0.6 % Eye Dam. 1; H318: C ≥ 0.6 % Eye Irrit. 2; H319: 0.06 % ≤ C < 0.6 % Skin Sens. 1A; H317: C ≥ 0.0015 %	≥0.00025-<0.0015%
---	--	-------------------

(Contd. on page 2)

GB

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 29.09.2021

Version number 6 (replaces version 5)

Revision: 13.11.2019

Identification of the substance/preparation: ESD Protect ESD-Oberflächenreiniger

(Contd. of page 1)

· **Regulation (EC) No 648/2004 on detergents / Labelling for contents**

preservation agents (2-BROMO-2-NITROPROPANE-1,3-DIOL, METHYLCHLOROISOTHIAZOLINONE / METHYLISOTHIAZOLINONE, OCTYLISOTHIAZOLINONE)

· **Additional information:** For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

· **4.1 Description of first aid measures**

- **General information:** Immediately remove any clothing soiled by the product.
- **After inhalation:** Supply fresh air; consult doctor in case of complaints.
- **After skin contact:** Generally the product does not irritate the skin.
- **After eye contact:**
Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.
- **After swallowing:** Rinse out mouth and then drink plenty of water.

· **4.2 Most important symptoms and effects, both acute and delayed**

No further relevant information available.

· **4.3 Indication of any immediate medical attention and special treatment needed**

No further relevant information available.

SECTION 5: Firefighting measures

· **5.1 Extinguishing media**

- **Suitable extinguishing agents:** Use fire extinguishing methods suitable to surrounding conditions.
- **For safety reasons unsuitable extinguishing agents:** Not applicable.

· **5.2 Special hazards arising from the substance or mixture** No further relevant information available.

· **5.3 Advice for firefighters**

· **Protective equipment:** No special measures required.

· **Additional information**

Dispose of fire debris and contaminated fire fighting water in accordance with official regulations.

SECTION 6: Accidental release measures

· **6.1 Personal precautions, protective equipment and emergency procedures** Not required.

· **6.2 Environmental precautions:** Do not allow to enter sewers/ surface or ground water.

· **6.3 Methods and material for containment and cleaning up:**

Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).

· **6.4 Reference to other sections**

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

SECTION 7: Handling and storage

· **7.1 Precautions for safe handling** No special precautions are necessary if used correctly.

· **Information about fire - and explosion protection:** No special measures required.

· **7.2 Conditions for safe storage, including any incompatibilities**

· **Storage:**

· **Requirements to be met by storerooms and receptacles:** No special requirements.

· **Information about storage in one common storage facility:** Not required.

· **Further information about storage conditions:** Store receptacle in a well ventilated area.

· **7.3 Specific end use(s)** No further relevant information available.

GB

(Contd. on page 3)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 29.09.2021

Version number 6 (replaces version 5)

Revision: 13.11.2019

Identification of the substance/preparation: ESD Protect ESD-Oberflächenreiniger

(Contd. of page 2)

SECTION 8: Exposure controls/personal protection

· **8.1 Control parameters**

· **Exposure limit values:**

The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.

· **Additional information:** The lists valid during the making were used as basis.

· **8.2 Exposure controls**

· **Appropriate engineering controls** No further data; see item 7.

· **Individual protection measures, such as personal protective equipment**

· **General protective and hygienic measures:** Wash hands before breaks and at the end of work.

· **Respiratory protection:** Not required.

· **Hand protection**

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation. Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

· **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

· **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **Eye/face protection** Goggles recommended during refilling

· **Body protection:** Light weight protective clothing

SECTION 9: Physical and chemical properties

· **9.1 Information on basic physical and chemical properties**

· **General Information**

· **Physical state**

Fluid

· **Colour:**

Colourless

· **Odour:**

Odourless

· **Odour threshold:**

Not determined.

· **Melting point/freezing point:**

0°C

· **Boiling point or initial boiling point and boiling range**

100°C

· **Flammability**

Not applicable.

· **Lower and upper explosion limit**

· **Lower:**

Not determined.

· **Upper:**

Not determined.

· **Flash point:**

Not applicable.

· **Auto-ignition temperature:**

Product is not selfigniting.

· **Decomposition temperature:**

Not determined.

· **pH at 20°C**

7.2

· **Viscosity:**

· **Kinematic viscosity**

Not determined.

· **Dynamic at 20°C:**

0.952 mPas

· **Solubility**

· **water:**

Not miscible or difficult to mix.

· **Partition coefficient n-octanol/water (log value)** Not determined.

(Contd. on page 4)

GB

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 29.09.2021

Version number 6 (replaces version 5)

Revision: 13.11.2019

Identification of the substance/preparation: ESD Protect ESD-Oberflächenreiniger

(Contd. of page 3)

· Vapour pressure at 20°C:	23 hPa
· Density and/or relative density	
· Density at 20°C:	0.995 g/cm ³
· Relative density	Not determined.
· Vapour density	Not determined.
9.2 Other information	
· Appearance:	
· Form:	Fluid
· Important information on protection of health and environment, and on safety.	
· Explosive properties:	Product does not present an explosion hazard.
· Solvent content:	
· Organic solvents:	0.0 %
· Change in condition	
· Evaporation rate	Not determined.

Information with regard to physical hazard classes	
· Explosives	Not applicable
· Flammable gases	Not applicable
· Aerosols	Not applicable
· Oxidising gases	Not applicable
· Gases under pressure	Not applicable
· Flammable liquids	Not applicable
· Flammable solids	Not applicable
· Self-reactive substances and mixtures	Not applicable
· Pyrophoric liquids	Not applicable
· Pyrophoric solids	Not applicable
· Self-heating substances and mixtures	Not applicable
· Substances and mixtures, which emit flammable gases in contact with water	Not applicable
· Oxidising liquids	Not applicable
· Oxidising solids	Not applicable
· Organic peroxides	Not applicable
· Corrosive to metals	Not applicable
· Desensitised explosives	Not applicable

SECTION 10: Stability and reactivity

- **10.1 Reactivity** see section "Possibility of hazardous reactions".
- **10.2 Chemical stability** No information available.
- **Conditions to avoid:** No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

GB

(Contd. on page 5)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 29.09.2021

Version number 6 (replaces version 5)

Revision: 13.11.2019

Identification of the substance/preparation: ESD Protect ESD-Oberflächenreiniger

(Contd. of page 4)

SECTION 11: Toxicological information

· **11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008**

· **Acute toxicity**

· **LD/LC50 values relevant for classification:**

52-51-7 bronopol (INN)

Oral	LD50	305 mg/kg (rat) (OECD 401)
------	------	----------------------------

Dermal	LD50	1,600 mg/kg (rabbit)
--------	------	----------------------

· **11.2 Information on other hazards**

· **Endocrine disrupting properties**

None of the ingredients is listed.

SECTION 12: Ecological information

· **12.1 Toxicity**

· **Aquatic toxicity:**

52-51-7 bronopol (INN)

LC50/96h	41.2 mg/l (Oncorhynchus mykiss (Rainbow trout))
----------	---

EC50/72h	0.4-2.8 mg/l (algae)
----------	----------------------

· **12.2 Persistence and degradability**

The surfactants contained in the product correspond to the legislation on the environmental compatibility of detergents and are biodegradable.

The solvent is biodegradable.

· **12.3 Bioaccumulative potential** No further relevant information available.

· **12.4 Mobility in soil** No further relevant information available.

· **12.5 Results of PBT and vPvB assessment**

· **PBT:** Not applicable.

· **vPvB:** Not applicable.

· **12.6 Endocrine disrupting properties**

The product does not contain substances with endocrine disrupting properties.

· **12.7 Other adverse effects**

· **Additional ecological information:**

· **General notes:**

Water hazard class 2 (German Regulation) (Self-assessment): hazardous for water

Do not allow product to reach ground water, water course or sewage system.

Danger to drinking water if even small quantities leak into the ground.

SECTION 13: Disposal considerations

· **13.1 Waste treatment methods**

· **Recommendation**

Must not be disposed together with household garbage. Do not allow product to reach sewage system.

· **Uncleaned packaging:**

· **Recommendation:** Disposal must be made according to official regulations.

SECTION 14: Transport information

· **14.1 UN number or ID number**

· **ADR, ADN, IMDG, IATA**

Not applicable

(Contd. on page 6)

GB

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 29.09.2021

Version number 6 (replaces version 5)

Revision: 13.11.2019

Identification of the substance/preparation: ESD Protect ESD-Oberflächenreiniger

(Contd. of page 5)

· 14.2 UN proper shipping name · ADR, ADN, IMDG, IATA	Not applicable
· 14.3 Transport hazard class(es) · ADR, ADN, IMDG, IATA · Class	Not applicable
· 14.4 Packing group · ADR, IMDG, IATA	Not applicable
· 14.5 Environmental hazards:	Not applicable.
· 14.6 Special precautions for user	Not applicable.
· 14.7 Maritime transport in bulk according to IMO instruments	Not applicable.
· UN "Model Regulation":	Not applicable

SECTION 15: Regulatory information

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Directive 2012/18/EU**
- **Named dangerous substances - ANNEX I** None of the ingredients is listed.
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· **Relevant phrases**

- H301 Toxic if swallowed.
- H310 Fatal in contact with skin.
- H314 Causes severe skin burns and eye damage.
- H317 May cause an allergic skin reaction.
- H318 Causes serious eye damage.
- H330 Fatal if inhaled.
- H400 Very toxic to aquatic life.
- H410 Very toxic to aquatic life with long lasting effects.

· **Abbreviations and acronyms:**

- ADR: Accord relatif au transport international des marchandises dangereuses par route (European Agreement Concerning the International Carriage of Dangerous Goods by Road)
- IMDG: International Maritime Code for Dangerous Goods
- IATA: International Air Transport Association
- GHS: Globally Harmonised System of Classification and Labelling of Chemicals
- EINECS: European Inventory of Existing Commercial Chemical Substances
- ELINCS: European List of Notified Chemical Substances
- CAS: Chemical Abstracts Service (division of the American Chemical Society)
- LC50: Lethal concentration, 50 percent
- LD50: Lethal dose, 50 percent
- PBT: Persistent, Bioaccumulative and Toxic
- vPvB: very Persistent and very Bioaccumulative
- Acute Tox. 3: Acute toxicity – Category 3
- Acute Tox. 2: Acute toxicity – Category 2
- Skin Corr. 1C: Skin corrosion/irritation – Category 1C
- Eye Dam. 1: Serious eye damage/eye irritation – Category 1
- Skin Sens. 1A: Skin sensitisation – Category 1A
- Aquatic Acute 1: Hazardous to the aquatic environment - acute aquatic hazard – Category 1
- Aquatic Chronic 1: Hazardous to the aquatic environment - long-term aquatic hazard – Category 1

GB