Constant Current LED Power Supply

SLT20-350IF-2S SLT20-700IF-2S





Product description:

This type of power supply is an exclusively designed stabilized power supply for LED lamp. With constant current (CC) technology, it is suitable for constant current lamps(350/700mA) connected in a series.

The built-in protection circuit will shut down the power supply in case of such faults as: open circuit, short circuit, over load or over temperature. The power supply will restart automatically after fault correction.

Standards:

EN61347-1

EN61347-2-13

EN61547

EN55015

EN61000-3-2

EN61000-3-3

EN62384

EN62493

Characteristics:

- Independent power supply for constant current LED lamp
- Special design screw terminal for field connection
- Class II protection against electric shock from direct and indirect contact
- SELV output
- Open circuit, short circuit, over load and over temperature protection
- Auto restart after fault conditions removal
- Efficiency ≥80% (AC230V,full load)

Official version: 04 Mar,2022

Page: 1 of 5




Specifications:

| Model | | SLT20-350IF-2S | SLT20-700IF-2S | | | | | |
|------------------|---|-----------------------|----------------|--|--|--|--|--|
| | turn on time(S) | ≤0.5 | ≤0.5 | | | | | |
| Output | output current(mA) | 350 | 700 | | | | | |
| | output current tolerance ⁰ | +/-5% | +/-5% | | | | | |
| | ripple current(%) | 3% | 3% | | | | | |
| | working voltage range(V) | 6-56 | 6-29 | | | | | |
| | Max. output voltage(V) | 59 | 40 | | | | | |
| | dimming interface | No | | | | | | |
| | dimming range | n/a | | | | | | |
| | rated supply voltage(Vac) | 220-240 | 220-240 | | | | | |
| | voltage range(Vac) | 198-264 | 198-264 | | | | | |
| | line frequency(Hz) | 50/60 | 50/60 | | | | | |
| Input | input current(mA) | 130 | 130 | | | | | |
| | efficiency ² | ≥80%@full load | ≥79%@full load | | | | | |
| | power factor | ≥0.85C | ≥0.85C | | | | | |
| | inrush current(lpk) | 12A/26us | 12A/26us | | | | | |
| Protection | over voltage protection | YES | YES | | | | | |
| | short circuit protection | YES | YES | | | | | |
| | over temperature protection | YES | YES | | | | | |
| | automatic restart | YES | YES | | | | | |
| | over load protection | YES | YES | | | | | |
| | surge capacity | L-N: 500V | L-N: 500V | | | | | |
| | Ta(°C) | -2045 | | | | | | |
| Ambient and Life | Tc max. (℃) | 85°C | | | | | | |
| | Storage Temperature(℃) | -3085 | | | | | | |
| | ambient humidity range | 5%85%, Not condensing | | | | | | |
| | nominal life-time(hrs) | 30000 | | | | | | |
| Other - | weight(g) | 69 | | | | | | |
| | dimensions (L×W×H)(mm) | 121x45x16 | | | | | | |
| | casing material | Plastic | | | | | | |
| | housing colour | Grey+Blue | | | | | | |
| | type of protection | IP20 | | | | | | |
| | protection class | ClassII | | | | | | |
| Note | 1.Tolerance: includes set up tolerance, line regulation and load regulation. 2.Tested at full load,230Vac.Refer to "Power Factor" and "EFFICIENT" curve graphs. 3.All parameters NOT specially mentioned are measured at nominal voltage input, rated load and 25 of ambient temperature. 4.The power supply is considered as a component that will be operated in combination with final equipment. Since EMC performance will be affected by the complete installation, the final equipment manufacturers must re-qualify EMC Directive on the complete installation again. | | | | | | | |
| | | | | | | | | |




Dimensions(mm):







Wiring diagram:





Electrical curves:





note
For constant current power supply, "LOAD" means the percentage of the maximum rated output voltage.
For constant voltage power supply, "LOAD" means the percentage of the maximum rated output current.



MCBS information:

| Miniature circuit breaker Model Model | B10 | B13 | B16 | B20 | C10 | C13 | C16 | C20 |
|--|-----|-----|-----|-----|-----|-----|-----|-----|
| SLT20-350IF-2S | 52 | 67 | 83 | 104 | 60 | 78 | 96 | 120 |
| SLT20-700IF-2S | 52 | 67 | 83 | 104 | 60 | 78 | 96 | 120 |

Sales & Technical Support:

Self Electronics Co.,Ltd.

Add: No. 1345 JuXian Road, Ningbo Hi Tech Park, Ningbo, China 315103 Phone: +86-574-2880-5765, +86-574-2880-5658 (for English assistance) +86-574-2880-5678 (for Chinese assistance)

Fax: +86-574-28805656

E-mail: sales@self-electronics.com http://www.self-electronics.com

Self Electronics Co., Ltd., Shenzhen Office

Add: Room2007, Xinglang Xuan, Xinghe Mingju, Fuming Road, Futian District, Shenzhen Tel: 0086-755-83558850, 83558851 Fax: 0086-755-83558840

SELF ELECTRONICS GERMANY GMBH

Add: August-Horch-Str. 7,51149 Cologne

Phone: +492203-18501-0 Fax: 492203-18501-199

E-mail: saleseu@self-electronics.com

*Due to continuous improvements and innovations, specifications are subjected to change without notice.

