

PRODUCT

Moisture Barrier Bag 3.6MIL

TECHNICAL DATASHEET




CONSTRUCTION

The 3.6MIL bag features an antistatic metallized polyester outer layer and an antistatic inner layer. In between are layers of static dissipative polyethylene, nylon and an aluminium foil shield.

FEATURES

- Protects electronics from moisture and static damage
- Opaque and light tight to offer additional protection
- Firm lamination and heat sealing offers superior resistance to vapour and oxygen ingress
- Surface resistance of 10^8 - 10^{11} Ohms
- These bags are ideal for transporting and storing moisture sensitive devices such as circuit boards and electronic components.
- Available in 3.6 / 4.4 and 6Mil thicknesses
- Flexible structure & easy to vacuum seal




CONFIGURATION(S)

Our bags are available in custom sizes or in several industry standard sizes. Bags are offered in a 3-seal configuration, with our standard flexographically printed artwork. Our bags can also be personalised with your company logo on bespoke orders. Minimum order quantities apply.

To request a quotation or for more information, please call **+44 (0)1473 836200** email info@antistat.co.uk or visit www.antistat.co.uk

IMPORTANT: This data sheet and its contents (the "Information") belong to Antistat or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Antistat assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Antistat was aware of the possibility of such loss or damage arising) is excluded. © 2021 Antistat.



CAUTION
This bag contains
MOISTURE SENSITIVE DEVICES

LEVEL

If blank, see adjacent bar code label

1. Calculated shelf life in sealed bag: 12 months at <40°C and <90% relative humidity (RH)
2. Peak package body temperature: _____ °C
If blank, see adjacent bar code label
3. After bag is opened, devices that will be subjected to reflow solder or other high temperature process must be
 - a) Mounted within: _____ hours of factory conditions
If blank, see adjacent label
<30°C / 60% RH, or
 - b) Stored per J-STD-033
4. Devices require bake, before mounting, if:
 - a) Humidity Indicator Card reads >10% for level 2a - 5a devices or > 60% for level 2 devices when read at 23 ± 5°C
 - b) 3a or 3b not met
5. If baking is required, refer to IPC/JEDEC J-STD-033 for bake procedure

Bag Seal Date: _____
If blank, see adjacent bar code label

Note: Level and body temperature defined by IPC/JEDEC J-STD-020

LEVEL	FLOOR LIFE (OUT OF THE BAG) AT FACTORY AMBIENT 30°C / 60% RH OR AS STATED
1	Unlimited at 30°C / 85% RH
2	1 Year
2a	4 Weeks
3	168 Hours
4	72 Hours
5	48 Hours
5a	24 Hours
6	Mandatory bake before use. After bake must be reflowed within the time limit specified on the label


BAG ARTWORK

Our moisture barrier bags are produced with the following sample artwork as standard. For further information on bespoke/printed orders, please contact one of our sales team. Please note there is a minimum order quantity of 20,000 bags on all custom printed bags.


Note: All of our custom moisture barrier bags are batch coded for QC traceability.

MOISTURE BARRIER BAG
ANT018MBB





THIS BAG IS RoHS COMPLIANT
CONFORMS TO IPC/JEDEC J-STD-033



ATTENTION
THIS BAG CONTAINS
MOISTURE & ELECTROSTATIC
SENSITIVE DEVICES



S

To request a quotation or for more information, please call **+44 (0)1473 836200**
email info@antistat.co.uk or visit www.antistat.co.uk

IMPORTANT: This data sheet and its contents (the "Information") belong to Antistat or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Antistat assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Antistat was aware of the possibility of such loss or damage arising) is excluded. © 2021 Antistat.

TEST CONDITIONS

The following results were taken under the following environmental test conditions:
 Temperature: 23°C / Humidity: 12%

ITEM	TEST METHOD	TYPICAL VALUE
Film Composition	N/A	PET/AL/NY/PE
Inner and Outer Resistance	STM.11.11	10 ⁸ - 10 ¹¹ Ohms
Moisture Vapour Transmission Rate	ASTM F 1249	<=0.035g/100sq/in / 24 hours
Tensile Strength	ASTM D882	7500 PSI
Puncture Resistance	ASTM F1306-90(2002)	24lbs
Heat Seal Temperature	-	300-410°F
Heat Seal Time	-	0.5-3.5 sec
Heat Seal Pressure	-	30-70 PSI
Seal Strength	GB/96-04-10	12lbs
Static Decay Time	IEC61340-5-1 (±1000 - ±100V)	≤2S

TEST CONDITIONS

The anti-static moisture barrier bag is tested accordant with the relevant test standard and requirements.

Test Item:	Test Method:	Measured Equipment(s):	MDL:
Lead (Pb)	IEC 62321:2008 Ed.1 Sec.8	ICP-OES	2mg/kg
Cadmium (Cd)	IEC 62321:2008 Ed.1 Sec.8	ICP-OES	2mg/kg
Mercury (Hg)	IEC 62321:2008 Ed.1 Sec.7	ICP-OES	2mg/kg
Hexavalent Chromium (Cr(VI))	IEC 62321:2008 Ed.1 Annex C	UV-Vis	2mg/kg
Polybrominated Biphenyls (PBBs)	IEC 62321:2008 Ed.1 Annex A	GC-MS	5mg/kg
Polybrominated Diphenyl Ethers (PBDEs)	IEC 62321:2008 Ed.1 Annex A	GC-MS	5mg/kg

EMI Shielding: Meets required range of EN 61340-5-1 tested per IEC 61340-2-3 and ANSI/ESD STM11.31

To request a quotation or for more information, please call **+44 (0)1473 836200**
 email info@antistat.co.uk or visit www.antistat.co.uk

IMPORTANT: This data sheet and its contents (the "Information") belong to Antistat or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Antistat assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Antistat was aware of the possibility of such loss or damage arising) is excluded. © 2021 Antistat.

PRODUCT CODE	DESCRIPTION	SIZE (inch)	SIZE (mm):	NOTES
018-0130	Moisture Barrier Bag 3.6Mil / 92 microns	4 x 6	102 x 152	Pack of 100
018-0131	Moisture Barrier Bag 3.6Mil / 92 microns	6 x 12	152 x 305	Pack of 100
018-0134	Moisture Barrier Bag 3.6Mil / 92 microns	6 x 26	152 x 660	Pack of 100
018-0001	Moisture Barrier Bag 3.6Mil / 92 microns	6 x 28	152 x 711	Pack of 100
018-0136	Moisture Barrier Bag 3.6Mil / 92 microns	8 x 10	203 x 254	Pack of 100
018-0410	Moisture Barrier Bag 3.6Mil / 92 microns	8 x 20	203 x 508	Pack of 100
018-0400	Moisture Barrier Bag 3.6Mil / 92 microns	10 x 20	254 x 508	Pack of 100
018-0401	Moisture Barrier Bag 3.6Mil / 92 microns	10 x 24	254 x 610	Pack of 100
018-0301	Moisture Barrier Bag 3.6Mil / 92 microns	10 x 26	254 x 660	Pack of 100
018-0137	Moisture Barrier Bag 3.6Mil / 92 microns	12 x 16	305 x 406	Pack of 100
018-0402	Moisture Barrier Bag 3.6Mil / 92 microns	12 x 20	305 x 508	Pack of 100
018-0007	Moisture Barrier Bag 3.6Mil / 92 microns	16 x 18	406 x 457	Pack of 100
018-0403	Moisture Barrier Bag 3.6Mil / 92 microns	18 x 18	457 x 457	Pack of 100
018-0293	Moisture Barrier Bag 3.6Mil / 92 microns	18 x 24	457 x 610	Pack of 100
018-0300	Moisture Barrier Bag 3.6Mil / 92 microns	22 x 24	559 x 610	Pack of 100
018-0304	Moisture Barrier Bag 3.6Mil / 92 microns	23 x 32	584 x 813	Pack of 100
018-0038	Moisture Barrier Bag 3.6Mil / 92 microns	26 x 19	680 x 400	Pack of 50
018-0015	Moisture Barrier Bag 3.6Mil / 92 microns	29 x 23	750 x 600	Pack of 50

Note: Other sizes and thicknesses available upon request.

To request a quotation or for more information, please call **+44 (0)1473 836200**
 email info@antistat.co.uk or visit www.antistat.co.uk

IMPORTANT: This data sheet and its contents (the "Information") belong to Antistat or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Antistat assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Antistat was aware of the possibility of such loss or damage arising) is excluded. © 2021 Antistat.