

PRODUCT

Black Carrier Tape


DESCRIPTION

The following table outlines the typical values for dissipative black polystyrene product(s) produced at Antistat.

	PROPERTY	TYPICAL VALUE	UNIT	TEST METHOD
Physical	Specific Gravity	1.09	g/cm ³	ASTM D-792
Tensile	Tensile Strength @ Yield	24	MPa	ASTM D-882(5)
	Tensile Elongation @ Break	16	%	ASTM D-882(5)
Thermal	Heat Distortion	75	°C	ISO 75
Electrical	Surface Resistance	1 x 10 ⁶ - 1 x 10 ⁹	Ohms	ANSI/ESD STM 11.13-2021

PRODUCT CODE	WIDTH	LENGTH	QUANTITY
029-1032	8mm	18 Inch	Carton of 4500 pcs
029-1033	12mm	18 Inch	Pack of 500 pcs
029-1106	8mm	12 Inch	Pack of 100 pcs

To request a quotation or for more information, please call **+44 (0)1473 836200**
 email info@antistat.co.uk or visit www.antistat.co.uk

IMPORTANT: This data sheet and its contents (the "Information") belong to Antistat or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The information is subject to change without notice and replaces all data sheets previously supplied. The information supplied is believed to be accurate but Antistat assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the information or use of it (including liability resulting from negligence or where Antistat was aware of the possibility of such loss or damage arising) is excluded. © 2023 Antistat.