

MATERIAL SAFETY DATA SHEET (MSDS)

Report No.: BCTC2301556166-8RN1

Applicant: SHENZHEN ABSORB KING DESICCANT CO.,
LIMITED

Product Name: silica-gel desiccant

Product Type: /

Tested Date: 2023-01-11

Issued Date: 2023-02-07

Prepared By: *Bear*

Approved By: *Saher Chen*

Shenzhen BCTC Testing Co., Ltd.



SHENZHEN

1 - Identification of the substance /preparation and of the company/undertaking**Product identifier**

Product name : silica-gel desiccant
Model number : /
Country of origin : /
Export country : /
CAS number : Refer to section 3
EINECS number : Refer to section 3
Molecular formula : Refer to section 3

Relevant identified uses of the substance or mixture and uses advised against


Relevant identified uses : No information available.
Uses advised against : No information available.

Details of the supplier of the safety data sheet

Manufacture name : SHENZHEN ABSORB KING DESICCANT CO., LIMITED
Address : Ensobo Co., Ltd., Building 38, Shenjiang Industrial Zone, Siqian Town,
Xinhui District, Jiangmen City, Guangdong Province
Telephone : /
E-mail : /

Emergency telephone number

Emergency phone : /



2 - Hazards Identification

Hazards Classification

In accordance with Regulation (EC) No 1272/2008(CLP), the sample is divided into the following hazard category.

Physical hazard : Not classified as a physical hazard class.

Health hazard : Not classified as a health hazard class.

Environment hazard : Not classified as a environment hazard class.

Label elements

The product does not need to be labelled in accordance with Regulation (EC) No 1272/2008(CLP) or respective national laws.

Other hazards

No data available.

Invasion route : Skin touch, Eyes touch, Inhalation, Ingestion

Health hazards : No know significant effects or critical hazard to health.

Environment hazards : No know significant effects or critical hazard to environment.

Burn & burst danger : The sample is not flammable.

3 - Composition / Information on Ingredients


Substance/preparation: Preparation				
Component/Substance	Molecular Formula	Percent of Content (%)	CAS Number	EINECS Number
Silicon dioxide	SiO ₂	99.6	14808-60-7	215-683-2
sodium oxide	Na ₂ O	0.17	1313-59-3	235-641-7
Aluminum oxide	Al ₂ O ₃	0.16	1344-28-1	215-691-6
Calcium oxide	CaO	0.04	1305-78-8	215-138-9
Iron(III) oxide	Fe ₂ O ₃	0.02	1309-37-1	215-168-2
Magnesium oxide	MgO	0.01	1309-48-4	215-171-9

4 - First Aid Measures

After skin contact	:	In case of irritation or sensitisation, wash off with soap and plenty of water. Take victim immediately to hospital. Consult a physician.
After eye contact	:	IF IN EYES: Rinse cautiously with water for several minutes. If eye irritation persists: Get medical advice/attention.
After inhalation	:	Supply with fresh air. Call a POISON CENTER/doctor, if you feel unwell. If swallowed, rinse mouth. Never give anything by mouth to an unconscious
After ingestion	:	person. If large quantities of this material are swallowed, immediately call a POISON CENTER or doctor/physician.
Most important symptoms and effects, both acute and delayed	:	No known symptoms or effects.
Indication of any immediate medical attention and special treatment needed	:	No data available.

5 - Fire Fighting Measures

Suitable Fire Extinguishing Media	:	Foam, carbon dioxide, dry chemical extinguishers.
Special Remarks On Fire Hazards	:	The sample is not flammable. The smoke of combustion may cause apnea, irritation. As soon as possible, remove the goods from fire to open place. For small fires, use dry chemical, carbon dioxide, water spray or alcohol-resistant foam. For large fires, Standing on the windward, Use water spray to cool fire-exposed containers.
Special Fire Fighting Procedures	:	Carbon monoxide, carbon dioxide, nitrogen oxides and other unidentified product.
Combustion Products	:	The staff must equipped with filter mask(full mask) or isolated breathing apparatus. The staff must wear the clothes which can defend the fire.
Protective Equipment	:	




6 - Accidental Release Measures

Personal precautions, protective equipment and emergency procedures	: Use personal protective equipment. Avoid breathing dust, smoke, vapours, mist or gas. Ensure adequate ventilation.
Measures for environment protection	: Remove all sources of ignition. Evacuate personnel to safe areas.
Methods and materials for containment and cleaning up	: Collect leaking, avoid environmental pollution, and prevent from spreading or entering into sewers, surface water and groundwater.
Additional information	: Pick up and arrange disposal without creating dust. Sweep up and shovel. Keep in suitable, closed containers for disposal.
	: Prevent birds or fish feeding by the drainage system, must be completely recycled.

7 - Handling and Storage

Precautions for safe handling	: Avoid formation of dust and aerosols. Avoid contact with skin and eyes. Operating personnel must train specially and follow close to the line of operating instruction.
Conditions for safe storage, including any incompatibilities	: Avoid accumulate dust. Wear suitable protective clothing, gloves and eye/face protection. Packing require seal.
	: Keep container tightly closed in a cool, well-ventilated place.
	: Keep away from sources of ignition - No smoking.
	: Keep separate with the oxidizing agent.
	: Equip with relevant type and quantities of the extinguishment instruments.
	: Keep the sample as a easy identification.



8 - Exposure Controls / Personal Protection

Maximum admissible concentration	: No standard yet.
Monitoring Method	: No data available. Equipped with an eyewash facility and a safety shower. Use adequate
Engineering Control	: general or local exhaust ventilation to keep airborne concentrations below the permissible exposure limits.
Respiratory Protection	: Wear suitable mask. If the dust density exceed in the air, must wear air-purifying respirators.
Eye Protection	: Wear suitable chemical safety goggles.
Body Protection	: Wear suitable safety cloth.
Hands Protection	: Wear suitable protective gloves.
Other Protection	: No smoking, dining and drinking water in the workplace. Keep good habit of hygiene. Shower and change clothes after work.

9 - Physical and Chemical Properties


Appearance	: Grain	Odor	: Unscented
Color	: Transparent	pH	: No data available.
Melting Point	: No data available.	Density	: No data available.
Boiling point	: No data available.	Flashing Point	: No data available.
Explosion Upper Limits	: No data available.	Explosion Lower Limits	: No data available.
Ignition temperature	: No data available.	Decomposition temperature	: No data available.
Solubility	: No data available.		

10 - Stability and Reactivity

Stability	: Stable under normal temperature and pressure
Conditions To Avoid	: Avoid fire, elevated temperatures, direct sunlight.
Possibility of hazard reactions	: No data available.
Incompatible materials	: Incompatible with acids, oxidizing agents, basis etc.
Hazardous Decomposition Products	: No data available.

11 - Toxicological Information

Acute Toxicity	: No data available.				
Skin corrosion/irritation	: No data available.				
Serious eye damage/ eye irritation	: No data available.				
Respiratory or skin Sensitization	: No data available.				
Germ cell mutagenicity	: No data available.				
Carcinogenicity	: IARC: No ingredients at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.				
Reproductive toxicity	: No data available.				
Specific target organ toxicity-single exposure	: No data available.				
Specific target organ toxicity-repeated exposure	: No data available.				
Aspiration hazard	: No data available.				
	<table border="0" style="margin-left: 20px;"> <tr> <td>Skin contact</td> <td>: Dust may cause irritation.</td> </tr> <tr> <td>Eye contact</td> <td>: Dust may cause irritation.</td> </tr> </table>	Skin contact	: Dust may cause irritation.	Eye contact	: Dust may cause irritation.
Skin contact	: Dust may cause irritation.				
Eye contact	: Dust may cause irritation.				
Potential invasion route	: <table border="0" style="margin-left: 20px;"> <tr> <td>Inhalation</td> <td>: May cause respiratory tract irritation, coughing, etc.</td> </tr> <tr> <td>Ingestion</td> <td>: If swallows, may cause discomfort, and effect people's digestive system.</td> </tr> </table>	Inhalation	: May cause respiratory tract irritation, coughing, etc.	Ingestion	: If swallows, may cause discomfort, and effect people's digestive system.
Inhalation	: May cause respiratory tract irritation, coughing, etc.				
Ingestion	: If swallows, may cause discomfort, and effect people's digestive system.				



12 - Ecological Information

Toxicity	: No data available.
Persistence and degradability	: No data available.
Bioaccumulative potential	: No data available.
Mobility in soil	: No data available.
Other adverse effects	: It might cause pollution when released large-scale to the air, water.

13 - Disposal Considerations

Nature of waste	: This product is not regarded as hazardous waste.
Waste disposal methods	: Offer surplus and non-recyclable solutions to a licensed disposal company. Refer to National or Local regulations before handling.
Attention abandoned	: Avoid abandon to the water.

14 - Transport Information**Transport Attentions:**

The products restrict the use of own steel tanker shipment when railway transport, submit to relevant departments for approval. The transport vehicles should be equipped with the appropriate variety and quantity of fire control equipment and emergency equipment for leakage. In summer, best transport in morning or evening. Transport tank should have grounding chain, the inner of tank should have baffle hole plate to reduce static electricity. Ban mixed operation with antioxidants, acid, alkali metal and amine. Prevent insoluble, rain and heat in transit. Keep away from fire, heat and high temperature when stopover.

Exhaust pipes of transport vehicle must be equipped with fire retardant equipment. Ban load and unload with mechanical equipments and tools that easy to produce the spark. According to prescribed routes when road transport. Do not stay in residential area and densely populated area. Ban humping when railway transport. Ban bulk transport use wooden boats, concrete boats.

Please refer to section 7-Handling and Storage also, and requirements of the ADR-RID/PG, IMO/IMDG/PG, IATA/ICAO/PG.

Maritime transport IMDG

IMDG Code : Non-dangerous goods
UN-Number : No data available.
Packing group : No data available.
Proper shipping name : No data available.

DOT regulations


Hazard class : Non-dangerous goods
UN-Number : No data available.
Packing group : No data available.
Proper shipping name : No data available.

Land transport ADR/RID(cross-border)

Hazard class : Non-dangerous goods
UN-Number : No data available.
Packing group : No data available.
Proper shipping name : No data available.

Air transport ICAO-TI and IATA-DGR

ICAO-TI-II class : Non-dangerous goods
UN/ID Number : No data available.
Packing group : No data available.
Proper shipping name : No data available.



15 - Regulatory Information**Safety, health and environmental regulations/legislation specific for the substance or mixture**

German regulations concerning the classification of hazard for water(WGK)	: Not listed.
Substance of Very High Concern (SVHC) according to Regulation (EC) No. 1907/2006 (REACH)	: Not listed.
The conditions of restrictions according to Regulation (EC) No. 1907/2006 (REACH) Article 67 and Annex XVII for the manufacturing, placing on the market and use must be observed	: Not listed.
Regulation (EC) No. 1907/2006 (REACH) Annex XVII (requiring authorization for use)	: Not listed.
Regulation (EC) No. 1907/2006 (REACH)-Pre-registered substance.	: Not listed.
Regulation (EC) No. 1005/2009 on substances that deplete the ozone layer	: Not listed.
Regulation (EC) No 649/2012 concerning the export and import of dangerous chemicals, Annex I	: Not listed.
ELINECS(European List of Notified Chemical Substances)	: Not listed.
Chemical Safety Assessment	: No data available.

16 - Other Information**Abbreviations and acronyms:**

ADR	: European Agreement concerning the International Carriage of Dangerous Goods by Road
CAS	: Chemical Abstracts Service
CLP	: Classification Packaging and Labelling
DOT	: US Department of Transportation
EC	: European Commission
EINECS	: The European Inventory of Existing Commercial Chemical Substances
IARC	: International Agency for Research on Cancer
IATA	: International Air Transport Association
ICAO	: International Civil Aviation Organization
IMDG	: International Maritime Dangerous Goods
RID	: Regulations Relating to International Carriage of Dangerous Goods by Rail
UN	: The United Nations

Disclaimer:

The information in this Material Safety Data Sheet (MSDS) was obtained from sources which we believe are reliable; however, the information is provided without any representation of warranty, expressed or implied, regarding the accuracy or correctness. The conditions or methods of handling, storage, use and disposal of the product are beyond our control and may be beyond our knowledge. For this and other reasons, we do not assume responsibility and expressly disclaim liability for loss, damage, or expense arising out of or in any way connected with the handling, storage, use, or disposal of this product. All information, recommendations, and suggestions appearing herein concerning this product are taken from sources or based upon data believed to be reliable.

Amendment:

-This report has revised the original test report Ref No: BCTC2301556166-8R, including the following additions and changes:

1. changes photo.

-After review, no additional test needed, all test data refer to the original report, and the original report is void.

Photograph of Sample



Fig.1




Fig.2

ST
C
ED
測





Fig.1



Fig.2



STATEMENT

1. The equipment lists are traceable to the national reference standards.
2. The test report can not be partially copied unless prior written approval is issued from our lab.
3. The test report is invalid without the "special seal for inspection and testing".
4. The test report is invalid without the signature of the approver.
5. The test process and test result is only related to the Unit Under Test.
6. Sample information is provided by the client and the laboratory is not responsible for its authenticity.
7. The test report without CMA mark is only used for scientific research, teaching, enterprise product development and internal quality control purposes.
8. The quality system of our laboratory is in accordance with ISO/IEC17025.
9. If there is any objection to this test report, the client should inform issuing laboratory within 15 days from the date of receiving test report.

Address:

1-2/F., Building B, Pengzhou Industrial Park, No.158, Fuyuan 1st Road, Zhancheng, Fuhai Subdistrict, Bao'an District, Shenzhen, Guangdong, China

TEL : 400-788-9558

P. C.: 518103

FAX : 0755-33229357

Website : <http://www.chnbctc.com>

E-Mail : bctc@bctc-lab.com.cn

***** END *****

2017