Taiwan Semiconductor

4A, 1000V Fast Recovery Bridge Rectifier

FEATURES

- Glass passivated chip junction
- Ideal for automated placement
- UL Recognized File # E-326854
- Moisture sensitivity level: level 1, per J-STD-020
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21

APPLICATIONS


- Switching mode power supply (SMPS)
- Adapters
- Lighting application

MECHANICAL DATA

- Case: TBS
- Molding compound meets UL 94V-0 flammability rating
- Matte tin plated leads, solderable per J-STD-002 •
- Meet JESD 201 class 1 whisker test
- Polarity: As marked
- Weight: 0.350g (approximately)

KEY PARAMETERS				
PARAMETER	VALUE	UNIT		
I _F	4	А		
V _{RRM}	1000	V		
I _{FSM}	110 A			
T _{J MAX}	150	°C		
Package	TBS			
Configuration	Quad			





ABSOLUTE MAXIMUM RATINGS (T _A = 25°C unless otherwise noted)					
PARAMETER		SYMBOL	RTBS40M	UNIT	
Marking code on the device			RT40M		
Repetitive peak reverse voltage		V _{RRM}	1000	V	
Reverse voltage, total rms value		V _{R(RMS)}	700	V	
Forward current		I _F	4	А	
Surge peak forward current, single half sine-wave superimposed on rated load	t = 8.3ms	1	110	А	
	t = 1.0ms	IFSM	290	А	
Rating for fusing (t<8.3ms)		l ² t	50.21	A ² s	
Junction temperature		TJ	-55 to +150	°C	
Storage temperature		T _{STG}	-55 to +150	°C	





THERMAL PERFORMANCE				
PARAMETER	SYMBOL	ТҮР	UNIT	
Junction-to-lead thermal resistance	R _{ejl}	17	°C/W	
Junction-to-ambient thermal resistance	R _{eja}	58	°C/W	
Junction-to-case thermal resistance	R _{eJC}	15	°C/W	

Thermal Performance Note: Units mounted on PCB (16mm x 16mm Cu pad test board)

ELECTRICAL SPECIFICATIONS (T _A = 25°C unless otherwise noted)					
PARAMETER	CONDITIONS	SYMBOL	ТҮР	MAX	UNIT
Forward voltage per diode ⁽¹⁾	I _F = 2A, T _J = 25°C	V _F	1.01	-	V
	$I_F = 4A, T_J = 25^{\circ}C$		1.10	1.30	V
	I _F = 2A, T _J = 125°C		0.85	-	V
	I _F = 4A, T _J = 125°C		0.95	1.17	V
Reverse current @ rated V_R per diode ⁽²⁾	$T_J = 25^{\circ}C$	I _R	-	5	μA
	T _J = 125°C		-	200	μA
Junction capacitance per diode	1MHz, V _R = 4.0V	CJ	32	-	pF
Reverse recovery time	$I_F = 0.5A, I_R = 1.0A$ $I_{rr} = 0.25A$	t _{rr}	-	300	ns

Notes:

1. Pulse test with PW = 0.3ms

2. Pulse test with PW = 30ms

ORDERING INFORMATION			
ORDERING CODE	PACKAGE	PACKING	
RTBS40M	TBS	1,800 / Tape & Reel	



CHARACTERISTICS CURVES

 $(T_A = 25^{\circ}C \text{ unless otherwise noted})$

Fig.1 Forward Current Derating Curve







Fig.3 Typical Reverse Characteristics



CAPACITANCE (pF)

Fig.2 Typical Junction Capacitance









RTBS40M Taiwan Semiconductor


PACKAGE OUTLINE DIMENSIONS



	DIM. Unit (mm		Unit ((inch)
	Min.	Max.	Min.	Max.
A1	0.00	0.15	0.000	0.006
A2	1.40	1.80	0.055	0.071
b	1.30	1.50	0.051	0.059
D	10.00	10.40	0.394	0.409
E	9.70	10.10	0.382	0.398
E1	6.80	7.20	0.268	0.283
е	4.90	5.10	0.193	0.201
L	0.50	1.10	0.020	0.043



SUGGESTED PAD LAYOUT



Symbol	Unit (mm)	Unit (inch)
A	1.00	0.039
В	1.50	0.059
С	5.00	0.197
D	9.25	0.364

MARKING DIAGRAM



P/N = Marking Co	de
------------------	----

- YW = Date Code
- F = Factory Code



Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.