

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name Canon Ink Bottle GI-51< Y >
Product code(s) 4548C

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use Ink for Ink Jet Printer

1.3. Details of the supplier of the safety data sheet

Supplier

Importer
Canon Europa N.V.
Bovenkerkerweg 59, 1185XB Amstelveen, The Netherlands
+31 20 5458545, +31 20 5458222
www.canon-europe.com, ceu-Reach@canon-europe.com

Manufacturer

Canon Inc.
30-2, Shimomaruko 3-Chome, Ohta-ku, Tokyo 146-8501, Japan

1.4. Emergency telephone number

Austria	+43 (0) 1 406 43 43	Belgium	+32 (0) 70 245 245
Bulgaria	+359 2 9154 233	Croatia	+385 (0)1-23-48-342
Cyprus	1401	Czech Republic	+420 224919293
Denmark	+45 82 12 12 12 ^[*1]	Estonia	16662
Finland	+358 (0)9 471977	France	+33 (0)1 45 42 59 59
Greece	+30 210 7793777	Hungary	+36 80 20 11 99
Ireland	353 (1) 809-2166/-2566	Italy	+39 (0)55 7947819
Latvia	+371 67042473	Lithuania	+370 (85) 2362052
Luxembourg	(+352) 8002 5500	Malta	21224071
Netherlands	+31 (0)30-2748888 ^[*2]	Poland	42 25 38-421/-422/-406
Portugal	+351 800 250 250	Romania	+40 21 318 36 06
Slovakia	+421 2 5477 4166	Slovenia	112
Spain	+34 91 562 04 20	Sweden	112 ^[*3]
United Kingdom	+44 121 507 4123	Iceland	112
Liechtenstein	145	Norway	+47 22 59 13 00
Switzerland	145		

*1 Kontakt Giftlinien på tlf.nr.: 82 12 12 12 (åbent 24 timer i døgnet). Se punkt 4 om førstehjælp.

*2 Only for the purpose of informing medical personnel in cases of acute intoxications.

*3 Ask for Poison Information

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008
Not classified

2.2. Label elements

Labelling according to Regulation (EC) No 1272/2008

Hazard pictograms

Not required

Signal word

Not required

Hazard statements

Not required

Precautionary statements

Not required

Other information

Contains 1,2-benzisothiazol-3(2H)-one.

May produce an allergic reaction.

Contains less than 30% of components with unknown hazards to the aquatic environment.

2.3. Other hazards

None

SECTION 3: Composition/information on ingredients**3.2. Mixtures**

Chemical name	CAS-No	EC-No	REACH registration number	Weight %	Classification (Reg. 1272/2008)	Note to other hazards
Glycerin	56-81-5	200-289-5	None	5 - 10	None	
Glycol	CBI	CBI	CBI	1 - 5	Eye Irrit. 2 (H319)	
Urea compound	CBI	CBI	CBI	1 - 5	Eye Irrit. 2 (H319) STOT RE 2 (thyroid gland) (H373)	
Azo dye	CBI	CBI	CBI	1 - 5	Aquatic Chronic 3 (H412)	
Water	7732-18-5	231-791-2	None	60 - 80	None	

Full texts of Hazard statement(s) are listed in SECTION 16

Note to other hazards : The following substance(s) is (are) marked with (1), (2) and/or (3)

- (1) Substance for which EU Occupational Exposure Limit(s) is (are) established (See SECTION 8)

- (2) PBT substance or vPvB substance under Regulation (EC) No 1907/2006

- (3) Substance listed in Candidate List of SVHC for Authorisation under Regulation (EC) No 1907/2006

In case a safety data sheet supplied under (EC) No 1907/2006 Article 31-3 is necessary, please contact us.

SECTION 4: First aid measures**4.1. Description of first aid measures****Inhalation**

Move to fresh air. Get medical attention immediately if symptoms occur.

Ingestion

Rinse mouth. Drink 1 or 2 glasses of water. Get medical attention immediately.

Skin contact

Wash off immediately with soap and plenty of water. Get medical attention immediately if symptoms occur.

Eye contact

Flush with plenty of water. Get medical attention immediately if symptoms occur.

4.2. Most important symptoms and effects, both acute and delayed**Inhalation**

None under normal use. Symptoms of overexposure are dizziness, headache, tiredness,

nausea, unconsciousness, cessation of breathing.

Ingestion

None under normal use. Ingestion may cause gastrointestinal irritation, nausea, vomiting and diarrhea.

Skin contact

None under normal use.

Eye contact

None under normal use. May cause slight irritation.

Chronic effects

None under normal use.

4.3. Indication of any immediate medical attention and special treatment needed

None

SECTION 5: Firefighting measures**5.1. Extinguishing media****Suitable extinguishing media**

Use CO₂, water, dry chemical, or foam.

Unsuitable extinguishing media

None

5.2. Special hazards arising from the substance or mixture**Special hazard**

None

Hazardous combustion products

Carbon dioxide (CO₂), Carbon monoxide (CO)

5.3. Advice for firefighters**Special protective equipment for firefighters**

None

SECTION 6: Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures**

Avoid contact with skin, eyes and clothing.

6.2. Environmental precautions

Keep out of waterways.

6.3. Methods and material for containment and cleaning up

Wipe up with adsorbent material (e.g. cloth, fleece).

6.4. Reference to other sections

None

SECTION 7: Handling and storage**7.1. Precautions for safe handling**

Avoid contact with skin, eyes and clothing. Clean contaminated surface thoroughly. Use with adequate ventilation.

7.2. Conditions for safe storage, including any incompatibilities

Keep in a dry, cool and well-ventilated place. Keep out of the reach of children. Keep away from direct sunlight. Keep away from heat and sources of ignition. Store upright and ensure that the cap of the bottle is tightly closed in order to avoid leakage or spillage of the ink.

7.3. Specific end uses

Ink for Ink Jet Printer. Obtain special instructions before use.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits

Chemical name	EU OEL	Austria	Belgium	Bulgaria	Cyprus
Glycerin 56-81-5	None	None	TWA: 10 mg/m ³	None	None
Chemical name	Czech Republic	Denmark	Finland	France	Germany
Glycerin 56-81-5	TWA: 10 mg/m ³ Ceiling: 15 mg/m ³	None	TWA: 20 mg/m ³	TWA: 10 mg/m ³	DFG TWA: 200 mg/m ³ inhalable fraction Ceiling / Peak: 400 mg/m ³ inhalable fraction
Chemical name	Greece	Hungary	Ireland	Italy	Netherlands
Glycerin 56-81-5	TWA: 10 mg/m ³	None	TWA: 10 mg/m ³ mist STEL: 30 mg/m ³ mist	None	None
Chemical name	Poland	Portugal	Romania	Slovakia	Spain
Glycerin 56-81-5	TWA: 10 mg/m ³ inhalable fraction	TWA: 10 mg/m ³ mist	None	None	TWA: 10 mg/m ³ mist
Chemical name	Sweden	United Kingdom	Norway	Switzerland	Turkey
Glycerin 56-81-5	None	TWA: 10 mg/m ³ mist	None	TWA: 50 mg/m ³ inhalable dust STEL: 100 mg/m ³ inhalable dust	None

8.2. Exposure controls

Appropriate engineering controls None under normal use conditions.

Individual protection measures, such as personal protective equipment

Eye/face protection	Not required under normal use.
Skin protection	Not required under normal use.
Respiratory protection	Not required under normal use.
Thermal hazards	Not applicable

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance	Yellow ; Liquid
Odor	Slight odor
Odor threshold	No data available
pH	7 - 9
Melting/freezing point (°C)	No data available
Boiling point/range (°C)	No data available
Flash point (°C)	> 93.0°C (Tag. Closed Cup.); estimated

Evaporation rate	No data available
Flammability (solid, gas)	Not applicable
Flammability limits in air	
Upper flammability limit	None; estimated
Lower flammability limit	None; estimated
Vapor pressure	No data available
Vapor density	No data available
Relative density	1.0 - 1.1
Solubility(ies)	Water; miscible
Partition coefficient: n-octanol/water	No data available
Auto-ignition temperature (°C)	None; estimated
Decomposition temperature (°C)	No data available
Viscosity (mPa s)	1 - 5
Explosive properties	None; estimated
Oxidizing properties	None; estimated

9.2. Other information

No data available

SECTION 10: Stability and reactivity

10.1. Reactivity

None

10.2. Chemical stability

Stable

10.3. Possibility of hazardous reactions

None

10.4. Conditions to avoid

None

10.5. Incompatible materials

Acids, Bases, Oxidizing agents, Reducing agents.

10.6. Hazardous decomposition products

Carbon dioxide (CO₂), Carbon monoxide (CO), and/or Ammonia.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity	No data available
Skin corrosion/irritation	Non-irritant (OECD Guideline)
Serious eye damage/eye irritation	Minimal irritant (OECD Guideline)
Sensitization	Non-sensitizer (OECD Guideline)
Germ cell mutagenicity	Ames test: Negative

Carcinogenicity	No data available
Reproductive toxicity	No data available
STOT - single exposure	No data available
STOT - repeated exposure	No data available
Aspiration hazard	No data available
Other information	No data available

SECTION 12: Ecological information

12.1. Toxicity

Ecotoxicity effects

No data available

12.2. Persistence and degradability

No data available

12.3. Bioaccumulative potential

No data available

12.4. Mobility in soil

No data available

12.5. Results of PBT and vPvB assessment

This preparation contains no substance considered to be persistent, bioaccumulating nor toxic (PBT).
This preparation contains no substance considered to be very persistent nor very bioaccumulating (vPvB).

12.6. Other adverse effects

No data available

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Dispose of in accordance with local regulations.

SECTION 14: Transport information

14.1. UN number None

14.2. UN proper shipping name None

14.3. Transport hazard class None

14.4. Packing group None

Issuing date : 02-Mar-2020

Revision date : -

4548C

Canon Ink Bottle GI-51< Y >

14.5. Environmental hazards

Not classified as environmentally hazardous under UN Model Regulations and marine pollutant under IMDG Code.

14.6. Special precautions for users

IATA: Not regulated

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

(EC) No 1907/2006 Authorisation	Not regulated
(EC) No 1907/2006 Restriction	Not regulated
(EC) No 1005/2009	Not regulated
(EU) 2019/1021	Not regulated
(EU) No 649/2012	Not regulated
Other information	None

15.2. Chemical safety assessment

None

SECTION 16: Other information

Full text of H-statements referred to under SECTION 2 and 3

H319 - Causes serious eye irritation

H373 - May cause damage to organs through prolonged or repeated exposure

H412 - Harmful to aquatic life with long lasting effects

Key literature references and sources for data

- World Health Organization International Agency for Research on Cancer, IARC Monographs on the Evaluation on the Carcinogenic Risk of Chemicals to Humans

- EU Regulation (EC) No 1907/2006, (EC) No 1272/2008, (EC) No 1005/2009, (EU) 2019/1021, (EU) No 649/2012

Key or legend to abbreviations and acronyms used in the safety data sheet

- PBT: Persistent, Bioaccumulative and Toxic

- vPvB: very Persistent and very Bioaccumulative

- SVHC: Substances of Very High Concern

- EU OEL: Occupational exposure limits at Union level under Directive 2004/37/EC, (EU) 2017/2398 and (EU) 2019/983, 98/24/EC, 91/322/EEC, 2000/39/EC, 2006/15/EC, 2009/161/EU and (EU) 2017/164.

- TWA: Time Weighted Average

- STEL: Short Term Exposure Limit

- GHS: Globally Harmonized System of Classification and Labelling of Chemicals

- IARC: International Agency for Research on Cancer

- IATA: International Air Transport Association

- CBI: Confidential Business Information

Issuing date : 02-Mar-2020

Revision date : -

Revision note : None

This product falls under (EC) No 1907/2006 Article 31-3.

Disclaimer

The information provided on this SDS is correct to the best of our knowledge, information and belief at the date of its

publication. The information given is designed only as a guide for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered as a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other material or in any process, unless specified in the text.