





Temperature Data Logger EBI 12

for food control during pasteurization, but also for monitoring, process and routine monitoring as well as temperature mapping...

BLUE LINE

The EBI 12 data logger is used for temperature measurement in canned food, jars, beverage cans and much more.

- High-quality stainless-steel housing
- Axial design
- M5 thread for attachment to the probe
- Application range from -40 °C to 140 °C
- High temperature accuracy of up to ±0.1 °C
- · Version with one measuring channels
- Temperature sensor 3 mm, rigid

Technical Data:

Operating temperature	-40 °C +140 °C
Measurement range	-40 °C +140 °C
Accuracy	± 0.2 °C (-40 °C 0 °C)
	± 0.1 °C (0 °C +140 °C)
Resolution	0.01 °C
Data memory	27,840 measurements
Sensor	PT1000, Class A
Measurement interval	1 s 24 hours
Real-time data	No
transmission	
Storage temperature	-20 °C +70 °C
Measurement modes	 endless measurement
	Measure upon starttime
	 Start immediately until end of
	memory
	Start- / Stop measurement
Battery	Lithium, 3.6 V,
•	User-replaceable
Dimensions	(Ø x H) 48 mm x 24 mm
Weight	app. 90 g
Housing material	316 L stainless steel / PEEK
Protection Class	IP68
Factory Calibration	-20 °C, 0 °C, +60 °C and +134 °C
Certificate	

EBI 12-T237



Standards and Directives:

- FCM EN 1935/2004
 Food Material Contact
- 2014/53/EU
 Radio Equipment Directive RED
- DIN EN 301 489
 Electro Magnetic Compatibility (EMC)

Туре	Description	Part No.
EBI 12-T237	L 100 mm	1340-6637

