

Lightweight and easy to use, these torches offer great manoeuvrability for smooth welding. The molded handle provides optimal grip to achieve the perfect weld. The SR 17 is a real bestseller and is particularly suitable for production work.

FEATURES

BASIC SR 17

Cooling: Air
Capacity:

- direct current (DC): 140 A
- in alternating current (AC): 125 A

Duty cycle: 60%.

Tungsten electrode: Ø 0.5 - 2.4 mm



GRIP SR 17

Cooling: Air
Capacity:

- direct current (DC): 140 A
- in alternating current (AC): 100 A


Duty cycle: 35%.

Tungsten electrode: Ø 0.5 - 2.4 mm



CONFIGURATIONS

Connector	l(m)	Ref	L	DB
Ø 10/25	4m	—	—	GRIP
	4m	044449	046030	
Ø 35/50	4m	044449	046030	
	8m	044340	046047	
EURO - connector (MIG)	4m	—	046108	



Included

All the essential consumables for your torch
TIG SR17 :

- 2 nozzles (N5 and N7)
- 2 collar supports (Ø1.6 + Ø2/2.4)
- 2 vice pliers (Ø1.6 + Ø2.4)
- 2 caps (1 short + 1 long)
- 2 tungsten electrodes WR2 AC/DC (Ø1.6 + Ø2.4)

• Also available for sale without the torch (ref. 044678)

CONSUMABLES

STANDARD ASSEMBLY

Nozzle	Collar support	Standard insulating ring	Collet	head cover
N 4 - Ø 6.5 (x3) 038394	Ø 1.6 (x3) 044968	(x1) 045040	Ø 1.6 (x3) 044982	Courte (x1) 044944
N 5 - Ø 8.0 (x3) 045026	Ø 2.0/2.4 (x3) 044975		Ø 2.0 (x3) 044999	Longue (x1) 044951
N 6 - Ø 9.5 (x3) 038400	Ø 3.2 (x3) 045118		Ø 2.4 (x3) 045019	
N 7 - Ø 11 (x3) 045033	Ø 4 (x3) 047648		Ø 3.2 (x3) 045125	
N 8 - Ø 12.5 (x3) 045286			Ø 4 (x3) 047655	
N 10 - Ø 16 (x3) 045293				
N 12 - Ø 19 (x3) 045309				

PRO MOUNTING

Diffuser nozzle	Support for diffuser collar	Insulating ring diffuser	Standard insulating ring	Collet	head cover
N5 - Ø 8.0 (x3) 045071	Ø 1.6 (x2) 045057	(x1) 045095	(x1) 045040	Ø 1.6 (x3) 044982	Courte (x1) 044944
N7 - Ø 11 (x3) 045088	Ø 2.0/2.4 (x2) 045064			Ø 2.0 (x3) 044999	Longue (x1) 044951
				Ø 2.4 (x3) 045019	

RECOMMENDATIONS

	TIG 160 DC	TIG 168 DC	TIG 200 DC FV	TIG 220 DC FV	TIG 300 DC	TIG 207 AC/DC FV	TIG 208 AC/DC	TIG 220 AC/DC	TIG 250 AC/DC
SR17 connection 10/25 + DIN	—	✓	✓	—	—	—	—	—	—
SR17 connection 35/50 + DIN	✓	✓	✓	—	—	—	—	—	—
SR17 connection EURO	Recommended for MIG/MAG generators with TIG function such as the MULTIPLEARL range.								