SAFETY DATA SHEET

Regulation (EC) No 1907/2006 (REACH) (COMMISSION REGULATION (EU) 2015/830)

Version 1 Product Name

AD66

Issue Date 14-Nov-2018
Revision date 23-May-2022

SECTION 1: Identification of the substance /mixture and of the company/undertaking

1.1. Product identifier

Product Name AD66

Product Code

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended Use Thermal grease

Uses advised against No information available

1.3. Details of the supplier of the safety data sheet

Supplier SHENZHENSHI TUODAYUAN TECHNOLOGY CO. LTD

Address

716, CHENGTOU BUSINESS CENTER, QINGLIN ROAD, HUANGGEKENG COMMUNITY,

LONGCHANG STREET, LANGGANG DISTRICT, SHENZHENSHI CHINA

Phone +86 755-2868-9466

Importer Address Postal Code Phone FAX E-mail

1.4. Emergency telephone number

Asia Pacific Tel:+886-2-2225-3517 China Tel: +86-21-51872177 Europe Tel: +31-(0)40-702-0900 North America Tel: +1-888-624-5099

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Not classified

2.2. Label elements

Symbols/Pictograms None Signal word None

Hazard Statements Not applicable Precautionary Statements Not applicable

2.3. Other hazards

No information available.

SECTION 3: Composition/information on ingredients

3.1 Mixture

Chemical Name	EC No	CAS No	Weight-%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
Aluminum	231-072-3	7429-90-5	81.4	Flam. Sol. 1 (H228)
				Water-react. 2 (H261)
Polysiloxane	-	63148-62-9	18.5	-
Silver Oxide	-	11113-88-5	0.1	-

SECTION 4: First aid measures

4.1. Description of first aid measures

General advice

In case of accident or unwellness, seek medical advice immediately (show directions for use or safety data sheet if possible).

Inhalation

IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing. Get medical advice/attention if you feel unwell.

Skin Contact

Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. Wash contaminated clothing before reuse. If skin irritation persists, call a physician.

Eye contact

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.

Ingestion

Rinse mouth. Get medical attention. Never give anything by mouth to an unconscious person.

4.2. Most important symptoms and effects, both acute and delayed

No information available.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media

No information available.

5.2. Special hazards arising from the substance or mixture

No information available.

5.3. Advice for firefighters

Evacuate personnel to safe areas. Move containers from fire area if you can do it without risk. Cool drums with water spray. Firefighters should wear self-contained breathing apparatus and full firefighting turnout gear. Stay upwind. Ensure adequate ventilation, especially in confined areas.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Evacuate personnel to safe areas. Ensure adequate ventilation, especially in confined areas. Remove all sources of ignition. Do not touch or walk through spilled material. Avoid contact with skin, eyes or clothing. Avoid generation of dust. Avoid breathing dust/fume/gas/mist/vapors/spray. Use personal protection recommended in Section 8.

6.2. Environmental precautions

Local authorities should be advised if significant spillages cannot be contained. Prevent entry into waterways, sewers, basements or confined areas.

6.3. Methods and material for containment and cleaning up

Contain and collect spillage with non-combustible absorbent material, (e.g. sand, earth, diatomaceous earth, vermiculite) and place in container for disposal according to local / national regulations (see Section 13).

6.4. Reference to other sections

See Section 7 for more information See section 8 for more information See section 13 for more information

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Handle in accordance with good industrial hygiene and safety practice. Ensure adequate ventilation, especially in confined areas. Avoid contact with skin, eyes or clothing. Wash contaminated clothing before reuse. Take precautionary measures against static discharges. Avoid generation of dust. Do not breathe dust/fume/gas/mist/vapors/spray. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Use personal protection recommended in Section 8.

7.2. Conditions for safe storage, including any incompatibilities

Keep containers tightly closed in a dry, cool and well-ventilated place. Keep away from heat. Keep locked up and out of reach of children. Store in accordance with local regulations.

7.3. Specific end use(s)

Apart from the uses mentioned in SECTION 1.2 no other specific uses are stipulated.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Chemical Name	Australia	Austria	Belgium	Denmark	European Union
Aluminum (CAS #:	10 mg/m ³	STEL 20 mg/m ³	-	TWA: 5 mg/m ³	-
7429-90-5)	5 mg/m₃	TWA: 10 mg/m ³		TWA: 2 mg/m ³	

Chemical Name	Latvia	France	Finland	Germany	Italy
Aluminum (CAS #:	TWA: 2 mg/m ³	TWA: 10 mg/m ³	TWA: 1.5 mg/m ³	TWA: 4 mg/m ³	-
7429-90-5)		TWA: 5 mg/m ³		TWA: 1.5 mg/m ³	

Chemical Name	Poland	Portugal	Spain	Switzerland	Netherlands
Aluminum (CAS #: 7429-90-5)	TWA: 2.5 mg/m ³ TWA: 1.2 mg/m ³	TWA: 10 mg/m³ TWA: 5 mg/m³	TWA: 10 mg/m ³ TWA: 5 mg/m ³	TWA: 3 mg/m ³	-

Chemical Name	Norway	United Kingdom	ACGIH TLV	OSHA PEL	NIOSH IDLH
Aluminum (CAS #:	TWA: 5 mg/m ³	STEL: 30 mg/m ³	TWA: 1 mg/m ³	TWA: 15 mg/m ³ total	TWA: 10 mg/m ³ total
7429-90-5)	STEL: 5 mg/m ³	STEL: 12 mg/m ³	respirable fraction	dust	dust
(200)	(~7.5)	TWA: 10 mg/m ³		TWA: 5 mg/m ³	TWA: 5 mg/m ³
		TWA: 4 mg/m ³	V-	respirable fraction	respirable dust TWA: 5
				(vacated) TWA: 15	mg/m³ Al
				mg/m ³ total dust	
				(vacated) TWA: 5	
-5-				mg/m ³ respirable	
(50)	.\			fraction (vacated)	
(20)				TWA: 5 mg/m ³ Al	
	/			Aluminum	1

Derived No Effect Level (DNEL)

No information available



Predicted No Effect Concentration (PNEC)

No information available

8.2. Exposure controls

Engineering Controls

Showers. Eyewash stations. Ensure adequate ventilation, especially in confined areas. Remove all sources of ignition.

Personal protective equipment

Eye/face protection Wear safety glasses with side shields (or goggles).

Hand Protection Wear protective gloves.
Skin and body protection Suitable protective clothing.

Respiratory protection In case of insufficient ventilation, wear suitable respiratory equipment.

Environmental exposure controls

Prevent entry into waterways, sewers, basements or confined areas.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance Paste Color Gray

Odor No information available

Odor Threshold

pH

Not determined

Not determined

Melting point/freezing point

Not determined

Boiling point / boiling range

Not determined

Flash point 200 °C

Evaporation rate Not determined Flammability (solid, gas) Not flammable Flammability Limit in Air Not applicable Vapor Pressure Not determined Vapor density Not applicable **Density** 2.5 g/cm³ Relative density Not determined Partition coefficient (LogPow) Not determined **Autoignition temperature** Not applicable **Decomposition temperature** Not determined Kinematic viscosity Not determined **Dynamic viscosity** Not determined **Explosive properties** Not an explosive **Oxidizing properties** Not determined

9.2. Other information

No information available

SECTION 10: Stability and reactivity

10.1. Reactivity

No information available.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

None under normal processing.

10.4. Conditions to avoid

Heat, flames and sparks.

10.5. Incompatible materials

None known based on information supplied.

10.6. Hazardous decomposition products

None under normal use conditions.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Aluminum (CAS #: 7429-90-5)	LD50> 15900 mg/kg bw(rat)	- (67)	LC50> 0.888 mg/L/4 h(rat)

Skin corrosion/irritation

Non-irritating to the skin.

Serious eye damage/eye irritation

No eye irritation.

Sensitization

No sensitization responses were observed.

Germ cell mutagenicity

No information available.

Carcinogenicity

No information available.

Reproductive toxicity

No information available.

STOT - single exposure

No information available

STOT - repeated exposure

No information available

Aspiration hazard

No information available.

SECTION 12: Ecological information

12.1. Toxicity

Chemical Name	Algae/aquatic plants EC50	Fish LC50	Crustacea EC50
Aluminum (CAS #: 7429-90-5)	-	> 50 mg/L/96h	-

12.2. Persistence and degradability

No information available.

12.3. Bioaccumulative potential

No information available.

12.4. Mobility in soil

No information available



12.5. Results of PBT and vPvB assessment

PBT/vPvB assessment information is not available as chemical safety assessment not conducted.

12.6. Other adverse effects

No information available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Waste from residues/unused products

Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated packaging

Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14: Transport information

14.1 UN Number Not regulated

14.2 Proper shipping name Not regulated

14.3 Hazard Class Not regulated

14.4 Packing Group Not regulated

14.5 Environmental hazards Non-marine pollutant

14.6 Special precautions No information available

14.7 Transport in bulk according to Annex II of

MARPOL 73/78 and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture European Union

Component	EINECS/ELINCS	SVHC candidates	RESTRICTIONS - REACH TITLE VIII	
Aluminum 7429-90-5 (81.4%)	X	10	-	

Take note of Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work

International Inventories

Component	TSCA	DSL/NDSL	ENCS	IECSC	KECL	PICCS	AICS
Aluminum 7429-90-5 (81.4%)	Х	х	Exempt	Х	Х	Х	Х

[&]quot;-" Not Listed

15.2. Chemical safety assessment

No information available

SECTION 16: Other information

This material safety data sheet complies with the requirements of Regulation (EC) No. 1907/2006



Take note of Directive 94/33/EC on the protection of young people at work

Take note of Directive 92/85/EC on the protection of pregnant and breastfeeding women at work

[&]quot;X" Listed

Issue Date14-Nov-2018Revision date23-May-2022Revision NoteNot applicable

Key or legend to abbreviations and acronyms used in the safety data sheet

TWA - TWA (time-weighted average)

STEL - STEL (Short Term Exposure Limit)

Ceiling - Maximum limit value

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

EINECS/ELINCS - European Inventory of Existing Chemical Substances/European List of Notified Chemical Substances

ENCS - Japan Existing and New Chemical Substances

IECSC - China Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

AICS - Australian Inventory of Chemical Substances

Full text of H-Statements referred to under section 3

H228 - Flammable solid

H261 - In contact with water releases flammable gases

Disclaimer

The information provided in this Material Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

