

## Highlights

- **4 levels**  
low, medium, high, turbo
- **Water tank volume**  
18 litres
- **Application area**  
25 m<sup>2</sup>
- **Operating time with full tank**  
12-15 hours
- **Ion cleaning function**  
Cleaning the ambient air
- **Operation**  
via touch control panel on the device or via the remote control
- **Insect repellent**  
Enjoy the summer without annoying mosquitoes



### 4 in 1: Cooling, humidifying, ventilating, repelling insects

The air cooler with 110 W output is the perfect solution for keeping your rooms pleasantly cool on hot days. With an air circulation of 1600 m<sup>3</sup>/hour, it provides a refreshing breeze for rooms up to 25 m<sup>2</sup> in size.

This innovative air cooler combines performance and comfort to provide you with a pleasant and cost-effective way to cool your room. The 18-litre water tank allows hours of operation without constant refilling. With a water evaporation rate of 1.2-1.5 litres per hour, this air cooler provides constant cooling and ensures a pleasant room climate.


With 4 speed settings, you can customise the cooling to suit your needs. Choose between low, medium, high and strong wind speed to achieve the optimum air circulation and temperature for your room. The integrated timer allows you to programme the operation of the air cooler according to your needs and save energy.



Front view



Oblique view



## Scope of delivery

- Air cooler
- Remote control
- Operating instructions

## Warranty period

- 2 years

## Specifications:

- Voltage: 220V-240V~ 50/60Hz
- Power: 110 W
- Water tank volume: 18 litres
- Application area: 25 m<sup>2</sup>
- Air circulation: 1600 m<sup>3</sup>/hour
- Water evaporation: 1.2-1.5 litres/hour
- 12-15 hours operating time with full tank
- 4 speed levels
- Swivelling function
- Insect repellent
- Ioniser
- timer
- Water level sensor

## Dimensions:

- Product (W×H×D): 345×1120×345 mm
- Packaging (W×H×D): 385×1200×385 mm
- Net/gross weight: 11.4 kg / 13.1 kg

