www.vishay.com


Vishay Siliconix

RoHS

COMPLIANT

FREE

Power MOSFET



PRODUCT SUMMARY				
V _{DS} (V)	100			
$R_{DS(on)}(\Omega)$	V _{GS} = 5.0 V 0.54			
Q _g (Max.) (nC)	6.1			
Q _{gs} (nC)	2.0			
Q _{gd} (nC)	3.3			
Configuration	Sin	gle		

FEATURES

- Dynamic dV/dt rating
- · Repetitive avalanche rated
- Surface-mount (IRLR110, SiHLR110)
- Straight lead (IRLU110, SiHLU110)
- · Available in tape and reel
- · Logic-level gate drive
- R_{DS(on)} specified at V_{GS} = 4 V and 5 V
- Material categorization: for definitions of compliance please see <u>www.vishav.com/doc?99912</u>

DESCRIPTION

Third generation ower MOSFETs from Vishay provide the designer with the best combination of fast switching, ruggedized device design, low on-resistance and cost-effectiveness.

The DPAK is designed for surface mounting using vapor phase, infrared, or wave soldering techniques. The straight lead version (IRLU, SiHLU series) is for through-hole mounting applications. Power dissipation levels up to 1.5 W are possible in typical surface-mount applications.

ORDERING INFORMATION					
Package	DPAK (TO-252)	DPAK (TO-252)	DPAK (TO-252)	IPAK (TO-251)	
Load (Dh) free and halogen free	SiHLR110-GE3	SiHLR110TR-GE3	-	SiHLU110-GE3	
Lead (Pb)-free and halogen-free	IRLR110PbF-BE3	IRLR110TRPbF-BE3	-	-	
Lead (Pb)-free	IRLR110PbF	IRLR110TRPbFa	IRLR110TRLPbF	IRLU110PbF	

Note

a. See device orientation

ABSOLUTE MAXIMUM RATINGS (T _C = 25 °C, unless otherwise noted)					
PARAMETER			SYMBOL	LIMIT	UNIT
Drain-source voltage			V_{DS}	100	V
Gate-source voltage			V_{GS}	± 10	v
Continuous duein surrent	\/ at 5 \/	T _C = 25 °C	1	4.3	
Continuous drain current $V_{GS} \text{ at 5 V} \qquad \frac{T_C = 25 \text{ °C}}{T_C = 100 \text{ °C}}$			l _D	2.7	А
Pulsed drain current ^a			I _{DM}	17	
Linear derating factor				0.20	W/°C
Linear derating factor (PCB mount) e				0.020	- VV/ C
Single pulse avalanche energy ^b			E _{AS}	100	mJ
Repetitive avalanche current a			I _{AR}	4.3	Α
Repetitive avalanche energy a			E _{AR}	2.5	mJ
Maximum power dissipation	T _C =	25 °C	В	25	W
Maximum power dissipation (PCB mount) e T _A = 25 °C			P_D	2.5	VV
Peak diode recovery dV/dt c			dV/dt	5.5	V/ns
Operating junction and storage temperature range			T _J , T _{stg}	-55 to +150	°C
Soldering recommendations (peak temperature) ^d	For	10 s		260	

Notes

- a. Repetitive rating; pulse width limited by maximum junction temperature (see fig. 11)
- b. $V_{DD} = 25 \text{ V}$, starting $T_J = 25 \,^{\circ}\text{C}$, $L = 8.1 \,\text{mH}$, $R_q = 25 \,\Omega$, $I_{AS} = 4.3 \,\text{A}$ (see fig. 12)
- c. $I_{SD} \le 5.6$ A, $dI/dt \le 140$ A/ μ s, $V_{DD} \le V_{DS}$, $T_J \le 150$ °C
- d. 1.6 mm from case
- e. When mounted on 1" square PCB (FR-4 or G-10 material)

S21-0818-Rev. D, 02-Aug-2021

IRLR110, IRLU110, SiHLR110, SiHLU110

Vishay Siliconix

THERMAL RESISTANCE RATINGS					
PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT
Maximum junction-to-ambient	R _{thJA}	-	-	110	
Maximum junction-to-ambient (PCB mount) ^a	R _{thJA}	-	-	50	°C/W
Maximum junction-to-case (drain)	R _{thJC}	-	-	5.0	

Note

a. When mounted on 1" square PCB (FR-4 or G-10 material)

PARAMETER	SYMBOL	TEST CONDITIONS		MIN.	TYP.	MAX.	UNIT
Static							
Drain-source breakdown voltage	V _{DS}	$V_{GS} = 0 \text{ V}, I_D = 250 \mu\text{A}$		100	-	-	V
V _{DS} temperature coefficient	$\Delta V_{DS}/T_{J}$	Reference	e to 25 °C, I _D = 1 mA	-	0.12	-	V/°C
Gate-source threshold voltage	V _{GS(th)}	V _{DS} =	V _{GS} , I _D = - 250 μA	1.0	-	2.0	V
Gate-source leakage	I _{GSS}	,	V _{GS} = ± 10 V	-		± 100	nA
Zoro goto voltago droip ourrent		V _{DS} =	: 100 V, V _{GS} = 0 V	-	-	25	
Zero gate voltage drain current	I _{DSS}	$V_{DS} = 80 \text{ V}$	$V_{GS} = 0 \text{ V}, T_{J} = 125 ^{\circ}\text{C}$	-	-	250	μA
Drain-source on-state resistance	D	V _{GS} = 5.0 V	$I_D = 2.6 A^b$	-	-	0.54	Ω
Diani-source on-state resistance	R _{DS(on)}	$V_{GS} = 4.0 \text{ V}$	$I_D = 2.2 A^b$	-	-	0.76	52
Forward transconductance	9fs	V _{DS} :	$= 50 \text{ V}, I_D = 2.6 \text{ A}$	2.3	-	-	S
Dynamic							
Input capacitance	C_{iss}		$V_{GS} = 0 V$,	-	250	-	
Output capacitance	C _{oss}	V _{DS} = 25 V, f = 1.0 MHz, see fig. 5		-	80	-	рF
Reverse transfer capacitance	C_{rss}			-	15	-	
Total gate charge	Q_g			-	-	6.1	
Gate-source charge	Q_gs	$V_{GS} = 5.0 \text{ V}$	$V_{GS} = 5.0 \text{ V}$ $I_D = 5.6 \text{ A}, V_{DS} = 80 \text{ V},$ see fig. 6 and 13 ^b		-	2.0	nC
Gate-drain charge	Q_gd		3	-	-	3.3	
Turn-on delay time	t _{d(on)}			-	9.3	-	
Rise time	t _r	V_{DD} = 50 V, I_{D} = 5.6 A, R_{g} = 12 Ω , R_{D} = 8.4 Ω , see fig. 10 ^b		-	47	-	ns
Turn-off delay time	$t_{d(off)}$			-	16	-	
Fall time	t _f			-	17	-	
Internal drain inductance	L _D	Between 6 mm (0.25	') from	-	4.5	-	nH
Internal source inductance	L _S	package and die conta	~ I H	-	7.5	-	''''
Drain-Source Body Diode Characteristic	cs						
Continuous source-drain diode current	Is	MOSFET sym showing the	bol	-	I	4.3	A
Pulsed diode forward current ^a	I _{SM}	integral reverse p - n junction diode		-	-	17	^
Body diode voltage	V_{SD}	T _J = 25 °C	I_{S} , I_{S} =4.3 A, V_{GS} = 0 V^{b}	_	-	2.5	V
Body diode reverse recovery time	t _{rr}	T 25 °C 1	- 5.6 A dl/dt - 100 A/vab		100	130	ns
Body diode reverse recovery charge	Q_{rr}	1J = 25 C, IF	$T_J = 25 ^{\circ}\text{C}, I_F = 5.6 \text{A}, \text{dI/dt} = 100 \text{A/} \mu \text{s}^{\text{b}}$		0.50	0.65	μC
Forward turn-on time	t _{on}	Intrinsic tu	rn-on time is negligible (turn	-on is dor	ninated b	y L _S and	L _D)

Notes

a. Repetitive rating; pulse width limited by maximum junction temperature (see fig. 11)

b. Pulse width \leq 300 μ s; duty cycle \leq 2 %

www.vishay.com

Vishay Siliconix

TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Fig. 1 - Typical Output Characteristics, T_C = 25 °C




Fig. 2 - Typical Transfer Characteristics




Fig. 1 - Typical Output Characteristics, T_C = 150 °C




Fig. 3 - Normalized On-Resistance vs. Temperature






Fig. 4 - Typical Capacitance vs. Drain-to-Source Voltage




Fig. 6 - Typical Source-Drain Diode Forward Voltage




Fig. 5 - Typical Gate Charge vs. Gate-to-Source Voltage




Fig. 7 - Maximum Safe Operating Area






Fig. 8 - Maximum Drain Current vs. Case Temperature




Fig. 10a - Switching Time Test Circuit




Fig. 10b - Switching Time Waveforms




Fig. 9 - Maximum Effective Transient Thermal Impedance, Junction-to-Case

Vishay Siliconix




Fig. 12a - Unclamped Inductive Test Circuit




Fig. 12b - Unclamped Inductive Waveforms




Fig. 12c - Maximum Avalanche Energy vs. Drain Current




Fig. 13a - Basic Gate Charge Waveform





Fig. 13b - Gate Charge Test Circuit



Peak Diode Recovery dV/dt Test Circuit







Fig. 10 - For N-Channel


Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see www.vishay.com/ppg?91323.




TO-252AA Case Outline

VERSION 1: FACILITY CODE = Y








	MILLIMETERS		
DIM.	MIN.	MAX.	
Α	2.18	2.38	
A1	-	0.127	
b	0.64	0.88	
b2	0.76	1.14	
b3	4.95	5.46	
С	0.46	0.61	
C2	0.46	0.89	
D	5.97	6.22	
D1	4.10	-	
E	6.35	6.73	
E1	4.32	-	
Н	9.40	10.41	
е	2.28	BSC	
e1	4.56	BSC	
L	1.40	1.78	
L3	0.89	1.27	
L4	-	1.02	
L5	1.01	1.52	

Note

• Dimension L3 is for reference only



VERSION 2: FACILITY CODE = N



	MILLIMETERS		
DIM.	MIN.	MAX.	
Α	2.18	2.39	
A1	-	0.13	
b	0.65	0.89	
b1	0.64	0.79	
b2	0.76	1.13	
b3	4.95	5.46	
С	0.46	0.61	
c1	0.41	0.56	
c2	0.46	0.60	
D	5.97	6.22	
D1	5.21	=	
E	6.35	6.73	
E1	4.32	-	
е	2.29 BSC		
Н	9.94	10.34	

	MILLIMETERS		
DIM.	MIN.	MAX.	
L	1.50	1.78	
L1	2.74	ł ref.	
L2	0.51	BSC	
L3	0.89	1.27	
L4	-	1.02	
L5	1.14	1.49	
L6	0.65	0.85	
θ	0°	10°	
θ1	0°	15°	
θ2	25°	35°	

Notes

- Dimensioning and tolerance confirm to ASME Y14.5M-1994
- All dimensions are in millimeters. Angles are in degrees
- Heat sink side flash is max. 0.8 mm
- Radius on terminal is optional

ECN: E19-0649-Rev. Q, 16-Dec-2019


DWG: 5347

www.vishay.com

Vishay Siliconix

Case Outline for TO-251AA (High Voltage)

OPTION 1:



	MILLIMETERS		INC	HES
DIM.	MIN.	MAX.	MIN.	MAX.
Α	2.18	2.39	0.086	0.094
A1	0.89	1.14	0.035	0.045
b	0.64	0.89	0.025	0.035
b1	0.65	0.79	0.026	0.031
b2	0.76	1.14	0.030	0.045
b3	0.76	1.04	0.030	0.041
b4	4.95	5.46	0.195	0.215
С	0.46	0.61	0.018	0.024
c1	0.41	0.56	0.016	0.022
c2	0.46	0.86	0.018	0.034
D	5.97	6.22	0.235	0.245

	MILLIMETERS		INC	HES
DIM.	MIN.	MAX.	MIN.	MAX.
D1	5.21	-	0.205	-
Е	6.35	6.73	0.250	0.265
E1	4.32	=	0.170	=
е	2.29	2.29 BSC		BSC
L	8.89	9.65	0.350	0.380
L1	1.91	2.29	0.075	0.090
L2	0.89	1.27	0.035	0.050
L3	1.14	1.52	0.045	0.060
θ1	0'	15'	0'	15'
θ2	25'	35'	25'	35'
	•		•	

ECN: E21-0682-Rev. C, 27-Dec-2021


DWG: 5968

Notes

- Dimensioning and tolerancing per ASME Y14.5M-1994
- Dimension are shown in inches and millimeters
- Dimension D and E do not include mold flash. Mold flash shall not exceed 0.13 mm (0.005") per side. These dimensions are measured at the outermost extremes of the plastic body
- Thermal pad contour optional with dimensions b4, L2, E1 and D1
- Lead dimension uncontrolled in L3
- Dimension b1, b3 and c1 apply to base metal only
- Outline conforms to JEDEC® outline TO-251AA



OPTION 2: FACILITY CODE = N



DIM.	MIN.	NOM.	MAX.
Α	2.180	2.285	2.390
A1	0.890	1.015	1.140
b	0.640	0.765	0.890
b1	0.640	0.715	0.790
b2	0.760	0.950	1.140
b3	0.760	0.900	1.040
b4	4.950	5.205	5.460
С	0.460	1	0.610
c1	0.410	-	0.560
c2	0.460	-	0.610
D	5.970	6.095	6.220
D1	4.300	- 1	ı

DIM.	MIN.	NOM.	MAX.
D2	5.380	-	-
E	6.350	6.540	6.730
E1	4.32	-	-
е	2.29	BSC	
L	8.890	9.270	9.650
L1	1.910	2.100	2.290
L2	0.890	1.080	1.270
L3	1.140	1.330	1.520
L4	1.300	1.400	1.500
θ1	0°	7.5°	15°
θ2	4°	-	-

ECN: E21-0682-Rev. C, 27-Dec-2021

DWG: 5968

Notes

- Dimensioning and tolerancing per ASME Y14.5M-1994
- All dimension are in millimeters, angles are in degrees
- Heat sink side flash is max. 0.8 mm



RECOMMENDED MINIMUM PADS FOR DPAK (TO-252)



Recommended Minimum Pads Dimensions in Inches/(mm)

Return to Index

APPLICATION NOTE



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.