



Knob Potentiometer



LINKS TO ADDITIONAL RESOURCES



The P16 is a revolutionary concept in panel mounted potentiometers. This unique design consists of a knob driving and incorporating a cermet potentiometer. Only the mounting hardware and terminals are situated on the back side of the panel reducing to a minimum the required clearance.

FEATURES







 P16 - version for professional and industrial applications (cermet)
 1 W at 40 °C

RoHS COMPLIANT

- PA16 version for professional audio applications (conductive plastic)
 0.5 W at 40 °C
- Compact (integrated)
- High dielectric strength: 2500 V_{RMS}
- Fully sealed and panel sealed
- Metallic or plastic knob options
- Custom knob on request
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

QUICK REFERENCE DATA				
Multiple module	No			
Switch module	n/a			
Detent module	n/a			
Special electrical laws	A: linear, L: logarithmic, F: reverse logarithmic			
Sealing level	IP 67			
Lifespan	50K cycles			







	D40	DA40	
B : :: .	P16 PA16		
Resistive element	Cermet Conductive plastic		
Electrical travel	270° ± 10°	270° ± 10°	
Power rating chart	0.25 PA16 LIN. TAPER PA16 LOG. TAPER NAME OF	80 100 120 140 EMPERATURE IN °C	
Circuit diagram	$ \begin{array}{c} \stackrel{\text{a}}{\circ} \longrightarrow \stackrel{\text{c}}{\circ} \\ \stackrel{\text{b}}{\circ} \longrightarrow \stackrel{\text{cw}}{\circ} \end{array} $		
Taper	100 80 80 F 60 40 0 20 0 0 20 40 60 80 100 % CLOCKWISE SHAFT ROTATION		
Resistance range logarithmic taper			
Standard series E3	1 - 2.2 - 4.7 and on request 1 - 2 - 5	1 - 2.2 - 4.7	
Tolerance standard	± 20 %	± 20 %	
on request	± 10 %	± 10 % (1 kΩ to 100 kΩ)	
Power rating logarithmic	1 W at +40 °C 0.5 W at +40 °C	0.5 W at +40 °C	
Femperature coefficient (typical)	± 150 ppm/°C	0.25 W at +40 °C ± 500 ppm/°C	
Dielectric strength (RMS)	2500 V	2500 V	
Limiting element voltage (linear law)	350 V	2500 V 350 V	
Contact resistance variation	3 % Rn or 3 Ω		
End resistance (typical)	3 % Hil or 3 Ω	2 % Rn or 3 Ω	
Insulation resistance (500 V _{DC})	10 ⁶ MΩ	$1~\Omega$ $10^6~\mathrm{M}\Omega$	



www.vishay.com

Vishay Sfernice

MECHANICAL SPECIFICATIONS				
Mechanical travel	300° ± 5°			
Operating torque	2 Ncm typical			
End stop torque	25 Ncm maximum			
Max. tightening torque of mounting nut	180 Ncm maximum			
Unit Weight	4.5 g typical			

ENVIRONMENTAL SPECIFICATIONS				
	METALLIC KNOB	PLASTIC KNOB		
Temperature range	-40 °C to +125 °C	-40 °C to +85 °C		
Climatic category	40/100/56	40/85/56		
Sealing	Sealed container and panel sealed			
Protection grades	IP67			

MARKING

- · Ohmic value code, tolerance code and taper
- Manufacturing date code

PACKAGING

• Carton box of 20 pieces

P16 STANDARD RESISTANCE ELEMENT DATA						
STAN-	LINEAR TAPER			LOG TAPER		
DARD RESIS- TANCE VALUES		MAX. VOLTAGE	MAX. CUR. THROUGH WIPER	MAX. POWER AT 40 °C	MAX. VOLTAGE	MAX. CUR. THROUGH WIPER
Ω	W	٧	mA	W	V	mA
22 47 100 220 470 1K 2.2K 4.7K 10K 22K 47K 100K 220K 470K 1M 2.2M 4.7M	1 1 1 1 1 1 1 1 1 1 0.56 0.26 0.12 0.05 0.02	4.69 6.85 10 14.8 21.7 31.6 46.9 68.5 100 148 217 316 350 350 350 350 350	213 146 100 67.4 46.1 31.6 21.3 14.6 10 6.74 4.61 3.16 1.59 0.75 0.35 0.07 0.012	0.5 0.5 0.5 0.5 0.5 0.5 0.5 0.5 0.5 0.5	7.1 10.5 15.3 22.4 33.2 48.5 70.7 105 153 224 332 350 350	71 48 32.6 22.4 15.1 10.3 7.07 4.77 3.26 2.24 1.51 0.74 0.35 0.16

CONTROL KNOB

Black metallic knob (NM).

Black plastic knob (NP).

For white, blue, red, and yellow color see ordering information. Other dimensions, shape, marking, colors of control knobs are manufactured on request - please consult Vishay.

Other reference marks (shapes, colors) and legends can be printed on plastic knob on request - please consult Vishay.

PA16 STANDARD RESISTANCE ELEMENT DATA						
STAN-	LI	NEAR TA	PER	LOG TAPER		
DARD RESIS- TANCE VALUES	MAX. POWER AT 40 °C	MAX. VOLTAGE		MAX. POWER AT 40 °C	MAX. VOLTAGE	MAX. CUR. THROUGH WIPER
Ω	W	٧	mA	W	V	mA
470 1K 2.2K 4.7K 10K 22K 47K 100K 220K 470K 1M	0.5 0.5 0.5 0.5 0.5 0.5 0.5 0.26 0.12	22.4 33.2 48.5 70.7 105 153 224 332 350 350	22.4 15.1 10.3 7.07 4.77 3.26 2.24 1.51 0.74 0.35	0.25 0.25 0.25 0.25 0.25 0.25 0.25 0.25	10.8 15.8 23.5 34.3 50.0 74 108 158 235 343	23.1 16 11 7 5.0 3.4 2.3 1.6 1.1




www.vishay.com


Vishay Sfernice

PERFORMANCE					
TESTS	CONDITIONS	TYPICAL VALUES AND DRIFTS			
12313		∆R _T /R _T (%)	$\Delta R_{1-2}/R_{1-2}$ (%)	OTHER	
Electrical endurance	1000 h at rated power 90'/30' cycle at +40 °C	± 5 %	-	Insulation resistance: $> 10^4 \ M\Omega$ Contact res. variation: $< 2 \ \%$ Rn	
Damp heat, steady state	56 days 40 °C, 93 % HR	± 2 %	± 1 %	Insulation resistance: $> 10^4 \text{ M}\Omega$	
Mechanical endurance	50 000 cycles	± 5 %	-	Contact res. variation: < 2 % Rn	
Shock	50 g's at 11 ms 3 successive shocks in 3 directions	± 0.2 %	± 0.5 %	-	
Vibration	10 Hz to 55 Hz 0.75 mm or 10 <i>g</i> 's during 6 h	± 0.2 %	-	$\Delta V_{1-2}/\Delta V_{1-3} \le \pm \ 0.5 \%$	

Note

· Nothing stated herein shall be construed as a guarantee of quality or durability





RELATED DOCUMENTS	
APPLICATION NOTES	
Potentiometers and Trimmers	www.vishay.com/doc?51001
Guidelines for Vishay Sfernice Resistive and Inductive Components	www.vishay.com/doc?52029



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.