

## Uninsulated Ring terminals 4.3 ... 10.5 mm (M4 - M10), for cables $\varnothing$ 0.5 ... 6 mm<sup>2</sup> 100 pcs set



RoHS



Quadrios uninsulated ring terminals guarantee optimal electrical and mechanical connections in conjunction with fitting crimping tools. This product series includes a variation of most used sizes, perfect for daily use. The ring terminals are especially suitable for hobbyists, craftsmen, field service, service workshops, electronics technicians and laboratory needs. Optimal for use with suitable ring terminal crimping pliers.

**Technical data:** Voltage (max.): 600 V, Material: copper (tin plated) • Hole diameter: 4.3 ... 10.5 mm • Thread size: M4 ... M10 • Cross-section: 0.5 ... 6 mm<sup>2</sup> • Content: 100 pcs pack.

Part No.	Description	Cross-section	Hole diameter	Thread size	EAN / GTIN	Content
23C496	Ring terminals M4, 0.5 - 1.5 mm <sup>2</sup> $\varnothing$ 4.3 mm	0.5 - 1.5 mm <sup>2</sup>	4.3 mm	M4	4260732284680	100 pcs
23C497	Ring terminals M5, 0.5 - 1.5 mm <sup>2</sup> $\varnothing$ 5.3 mm	0.5 - 1.5 mm <sup>2</sup>	5.3 mm	M5	4260732284697	100 pcs
23C498	Ring terminals M6, 0.5 - 1.5 mm <sup>2</sup> $\varnothing$ 6.5 mm	0.5 - 1.5 mm <sup>2</sup>	6.5 mm	M6	4260732284703	100 pcs
23C499	Ring terminals M8, 0.5 - 1.5 mm <sup>2</sup> $\varnothing$ 8.5 mm	0.5 - 1.5 mm <sup>2</sup>	8.5 mm	M8	4260732284710	100 pcs
23C500	Ring terminals M10, 0.5 - 1.5 mm <sup>2</sup> $\varnothing$ 10.5 mm	0.5 - 1.5 mm <sup>2</sup>	10.5 mm	M10	4260732284727	100 pcs
23C501	Ring terminals M4, 1.5 - 2.5 mm <sup>2</sup> $\varnothing$ 4.3 mm	1.5 - 2.5 mm <sup>2</sup>	4.3 mm	M4	4260732284734	100 pcs
23C502	Ring terminals M5, 1.5 - 2.5 mm <sup>2</sup> $\varnothing$ 5.3 mm	1.5 - 2.5 mm <sup>2</sup>	5.3 mm	M5	4260732284741	100 pcs
23C503	Ring terminals M6, 1.5 - 2.5 mm <sup>2</sup> $\varnothing$ 6.5 mm	1.5 - 2.5 mm <sup>2</sup>	6.5 mm	M6	4260732284758	100 pcs
23C504	Ring terminals M8, 1.5 - 2.5 mm <sup>2</sup> $\varnothing$ 8.5 mm	1.5 - 2.5 mm <sup>2</sup>	8.5 mm	M8	4260732284765	100 pcs
23C505	Ring terminals M10, 1.5 - 2.5 mm <sup>2</sup> $\varnothing$ 10.5 mm	1.5 - 2.5 mm <sup>2</sup>	10.5 mm	M10	4260732284772	100 pcs
23C506	Ring terminals M4, 2.5 - 4 mm <sup>2</sup> $\varnothing$ 4.3 mm	2.5 - 4 mm <sup>2</sup>	4.3 mm	M4	4260732284789	100 pcs
23C507	Ring terminals M5, 2.5 - 4 mm <sup>2</sup> $\varnothing$ 5.3 mm	2.5 - 4 mm <sup>2</sup>	5.3 mm	M5	4260732284796	100 pcs
23C508	Ring terminals M6, 2.5 - 4 mm <sup>2</sup> $\varnothing$ 6.5 mm	2.5 - 4 mm <sup>2</sup>	6.5 mm	M6	4260732284802	100 pcs
23C509	Ring terminals M8, 2.5 - 4 mm <sup>2</sup> $\varnothing$ 8.5 mm	2.5 - 4 mm <sup>2</sup>	8.5 mm	M8	4260732284819	100 pcs
23C510	Ring terminals M10, 2.5 - 4 mm <sup>2</sup> $\varnothing$ 10.5 mm	2.5 - 4 mm <sup>2</sup>	10.5 mm	M10	4260732284826	100 pcs
23C511	Ring terminals M4, 4 - 6 mm <sup>2</sup> $\varnothing$ 4.3 mm	4 - 6 mm <sup>2</sup>	4.3 mm	M4	4260732284833	100 pcs
23C512	Ring terminals M5, 4 - 6 mm <sup>2</sup> $\varnothing$ 5.3 mm	4 - 6 mm <sup>2</sup>	5.3 mm	M5	4260732284840	100 pcs
23C513	Ring terminals M6, 4 - 6 mm <sup>2</sup> $\varnothing$ 6.5 mm	4 - 6 mm <sup>2</sup>	6.5 mm	M6	4260732284857	100 pcs
23C514	Ring terminals M8, 4 - 6 mm <sup>2</sup> $\varnothing$ 8.5 mm	4 - 6 mm <sup>2</sup>	8.5 mm	M8	4260732284864	100 pcs
23C515	Ring terminals M10, 4 - 6 mm <sup>2</sup> $\varnothing$ 10.5 mm	4 - 6 mm <sup>2</sup>	10.5 mm	M10	4260732284871	100 pcs

Connection only by qualified electricians!